

Crimping pliers - CRIMPFOX 16 S - 1207983

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers for ferrules up to 16 mm²

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 980641
GTIN	4017918980641

Technical data

Dimensions

Length (b)	195 mm
Width (a)	63 mm

General

Color	black
Compression	Square crimp
Min. cross section	10 mm ²
Max. cross section	16 mm ²
AWG min	8
AWG max	6
Weight	300 g
Min. cross section	10 mm ²
Max. cross section	16 mm ²
AWG min	8
AWG max	6

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Crimping pliers - CRIMPFOX 16 S - 1207983

Classifications

eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

Crimping pliers - CRIMPFOX 16 S - 1207983

Approvals

EAC



RU x-
DE.xx08.B.02974

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1207983](#)