

Conductor marker carrier - PATG 6/23 - 0808037

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 14 ... 22 mm, lettering field size: 23 x 4 mm

Your advantages

- ✓ The corresponding UC-WMT ..., US-WMT ..., UCT-WMT ... and EMT ... insert labels are used for marking
- ✓ These conductor marking systems consist of marker carriers and insert labels
- ✓ The PATG ... collar is a captive marker carrier
- ✓ Can be used to mark conductors with a diameter of 0.6 ... 50 mm

RoHS

Key Commercial Data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 017918 168902
GTIN	4017918168902

Technical data

Dimensions

Length (b)	23 mm
Width (a)	18.6 mm
Cable diameter	14 mm ... 22 mm

Ambient conditions

Ambient temperature (operation)	-50 °C ... 80 °C
---------------------------------	------------------

General

Color	transparent
Type	Profile
Components	Silicone-free
Flammability rating according to UL 94	V0

Conductor marker carrier - PATG 6/23 - 0808037

Technical data

General

Material	PVC
RoHS compliant	Yes
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Marking mounting type	slide-on

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27149100
eCl@ss 7.0	27149153
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC002248
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0808037