

Torque screwdriver - TSD 20 SAC - 1212020

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Torque screwdriver, with preset torque of 2.0 Nm and 4 mm hexagonal drive for the pressure nut of the fast connection

The figure shows the TSD 04 SAC version

Your advantages

- ✓ Wide range of SAC... nuts for various different applications
- ✓ For the TSD-M... torque screwdrivers, the torque can be custom-set
- ✓ The TSD-M... adapters can accommodate the various nuts
- ✓ TSD ... SAC torque screwdrivers with a range of preset torques from 0.2 Nm to 2.5 Nm

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 439305
GTIN	4046356439305

Technical data

Dimensions

Length (b)	205 mm
Width (a)	37 mm
Blade thickness	0 mm
Blade width	0 mm
Blade height	100 mm

General

Color	black
Type	Hexagonal SW4

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Torque screwdriver - TSD 20 SAC - 1212020

Classifications

eCl@ss

eCl@ss 10.0.1	21040417
eCl@ss 4.0	21040400
eCl@ss 4.1	21040400
eCl@ss 5.0	21040400
eCl@ss 5.1	21040400
eCl@ss 6.0	21040400
eCl@ss 7.0	21040417
eCl@ss 8.0	21040417
eCl@ss 9.0	21040417

ETIM

ETIM 3.0	EC000158
ETIM 4.0	EC000158
ETIM 5.0	EC002132
ETIM 6.0	EC002132
ETIM 7.0	EC002132

UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

Torque screwdriver - TSD 20 SAC - 1212020

Accessories

Accessories

Screwdriver tools

Tool - SAC BIT QUICKON-W13 - 1212033



Nut for assembling pressure nuts with 13 mm wrench size, for 4 mm hexagonal drive

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212020](#)