

Screw insert - SF-BIT-SL 0,6X3,5-70 - 1212569

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Screw bit, slot, E6.3-1/4" drive, Size: 0.6 x 3.5 x 70 mm, hardened, suitable for holders as per DIN 3126-F 6.3 / ISO 1173

Your advantages

- ✓ Tools for SF-ASD 21 cordless screwdriver in various versions

Key Commercial Data

Packing unit	5 pc
GTIN	 4 046356 590044
GTIN	4046356590044

Technical data

Dimensions

Length (b)	70 mm
Blade thickness	0.6 mm
Blade width	3.5 mm
Blade height	70 mm

General

Color	silver
Type	Bladed
Material	Steel
Test standard	DIN 3126 drive, output 3127-1

Standards and Regulations

Test standard	DIN 3126 drive, output 3127-1
---------------	-------------------------------


Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Drawings

Screw insert - SF-BIT-SL 0,6X3,5-70 - 1212569

Pictogram



Classifications

eCl@ss

eCl@ss 10.0.1	21044204
eCl@ss 4.0	21040400
eCl@ss 4.1	21040400
eCl@ss 5.0	21040400
eCl@ss 5.1	21040400
eCl@ss 6.0	21049200
eCl@ss 7.0	21044204
eCl@ss 8.0	21044204
eCl@ss 9.0	21044204

Screw insert - SF-BIT-SL 0,6X3,5-70 - 1212569

Classifications

ETIM

ETIM 4.0	EC002115
ETIM 5.0	EC002116
ETIM 6.0	EC002116
ETIM 7.0	EC002116

UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701
UNSPSC 18.0	27112814
UNSPSC 19.0	27112814
UNSPSC 20.0	27112814
UNSPSC 21.0	27112814

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01750
-----	---	--------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212569](#)