

## Flat-nosed pliers - MICROFOX-F ESD\_DB - 1212797

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




ESD electronic flat-nose pliers, smooth gripping surface, with opening spring, non-reflective coating and phosphate-treated, 2-component handle, type of packaging: with holder for sales display (backcard)

### Your advantages

- ✓ Ergonomically designed two-component handles for fatigue-proof and non-slip use
- ✓ Opening spring for uniform, smooth opening
- ✓ Mirror-polished and phosphate-treated metal surfaces for optimum rust protection and no glare when working
- ✓ Screwed precision-joint for permanent stability and optimum results
- ✓ Made from special high-grade tool steel
- ✓ The special conductive plastic handles ensure slow and safe removal of electrostatic energy according to standards and directives such as DIN EN 61340-5



### Key Commercial Data

|              |   |
|--------------|---|
| Packing unit | 6 pc  |
| GTIN         | <br>4 046356 995030 |
| GTIN         | 4046356995030   |

### Technical data

#### Dimensions

|            |        |
|------------|--------|
| Length (b) | 125 mm |
|------------|--------|

#### General

|        |      |
|--------|------|
| Weight | 75 g |
|--------|------|

#### Environmental Product Compliance

|                           |   |
|---------------------------|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |
|---------------------------|---|

### Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 21043817 |
|---------------|----------|

## Flat-nosed pliers - MICROFOX-F ESD\_DB - 1212797

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 21040300 |
| eCl@ss 4.1 | 21040300 |
| eCl@ss 5.0 | 21040300 |
| eCl@ss 5.1 | 21040300 |
| eCl@ss 6.0 | 21043800 |
| eCl@ss 7.0 | 21043817 |
| eCl@ss 8.0 | 21043817 |
| eCl@ss 9.0 | 21043817 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC001186 |
| ETIM 3.0 | EC001186 |
| ETIM 4.0 | EC000833 |
| ETIM 5.0 | EC000833 |
| ETIM 6.0 | EC000833 |
| ETIM 7.0 | EC000833 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 27112126 |
| UNSPSC 18.0   | 27112126 |
| UNSPSC 19.0   | 27112126 |
| UNSPSC 20.0   | 27112126 |
| UNSPSC 21.0   | 27112126 |

### Approvals

#### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approval details

## Flat-nosed pliers - MICROFOX-F ESD\_DB - 1212797

### Approvals

EAC



RU x-  
DE.xx08.B.02974

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1212797