

Diagonal cutter - MICROFOX-S ESD_DB - 1212804

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




ESD electronic diagonal cutter, round head, without chamfer, with opening spring, non-reflective coating and phosphate-treated, 2-component handle, cutting capacity diameter: soft 0.2 ... 2.0 mm; medium hard 1 mm, type of packaging: with holder for sales display (backcard)

Your advantages

- ✓ Ergonomically designed two-component handles for fatigue-proof and non-slip use
- ✓ Opening spring for uniform, smooth opening
- ✓ Made from special high-grade tool steel
- ✓ Screwed precision-joint for permanent stability and optimum results
- ✓ Mirror-polished and phosphate-treated metal surfaces for optimum rust protection and no glare when working
- ✓ The special conductive plastic handles ensure slow and safe removal of electrostatic energy according to standards and directives such as DIN EN 61340-5



Key Commercial Data

Packing unit	6 pc
GTIN	 4 046356 994675
GTIN	4046356994675

Technical data

Dimensions

Length (b)	110 mm
------------	--------

General

Weight	70 g
--------	------

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	21043711
---------------	----------

Diagonal cutter - MICROFOX-S ESD_DB - 1212804

Classifications

eCl@ss

eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043700
eCl@ss 7.0	21043711
eCl@ss 8.0	21043711
eCl@ss 9.0	21043711

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC000165
ETIM 5.0	EC000165
ETIM 6.0	EC000165
ETIM 7.0	EC000165

UNSPSC

UNSPSC 13.2	27111511
UNSPSC 18.0	27111511
UNSPSC 19.0	27111511
UNSPSC 20.0	27111511
UNSPSC 21.0	27111511

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212804](#)