

Magnetic label - PMM (EX50)R - 1014315

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Magnetic label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: magnetic adhesion, lettering field size: 15000 x 50 mm, Number of individual labels: 1

Your advantages

- ✓ Magnetic labels, unprinted
- ✓ The magnetic labels supplied in rolls represent an individual and flexible marking solution, e.g., for warehouse marking.
- ✓ High adhesive strength
- ✓ The flexible magnetic tape will also adhere to round objects with a radius from 12 mm
- ✓ Magnetic tape coated with polyester foil

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 786195
GTIN	4046356786195

Technical data

Dimensions

Length (b)	15000 mm
Width (a)	50 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 55 °C
---------------------------------	------------------

General

Color	white
Material	Magnetic tape
Coating	Polyester foil
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	1
Number of individual labels per row	1

Magnetic label - PMM (EX50)R - 1014315

Technical data

General

Marking mounting type	magnetic adhesion
-----------------------	-------------------

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27149100
eCl@ss 5.1	27371300
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

ETIM

ETIM 3.0	EC000712
ETIM 4.0	EC002498
ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Ink ribbon

Magnetic label - PMM (EX50)R - 1014315

Accessories

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., width: 110 mm, color: black

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1014315