

## DIN rail perforated - NS 35/15 ZN PERF 2000MM - 1206599

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail perforated, Standard profile, width: 35 mm, height: 15 mm, similar to EN 60715, material: Steel, galvanized, length: 2000 mm, color: silver

RoHS

### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 5 pc                                                                                                    |
| Minimum order quantity | 5 pc                                                                                                    |
| GTIN                   | <br>4 017918 173050 |
| GTIN                   | 4017918173050                                                                                           |

### Technical data

#### Dimensions

|                    |          |
|--------------------|----------|
| Height             | 15 mm    |
| Length             | 2000 mm  |
| Width              | 35 mm    |
| Hole width         | 15.00 mm |
| Hole height        | 6.20 mm  |
| Drill hole spacing | 25.00 mm |

#### General

|          |            |
|----------|------------|
| Material | Steel      |
| Coating  | galvanized |
| Color    | silver     |


#### Standards and Regulations

|                                  |                     |
|----------------------------------|---------------------|
| Test standard                    | similar to EN 60715 |
| Connection in acc. with standard | IEC / EN            |

### Drawings

## DIN rail perforated - NS 35/15 ZN PERF 2000MM - 1206599

Dimensional drawing



### Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27400602 |
| eCl@ss 4.0    | 27110800 |
| eCl@ss 4.1    | 27110800 |
| eCl@ss 5.0    | 27141100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27400600 |
| eCl@ss 7.0    | 27400602 |
| eCl@ss 8.0    | 27400602 |
| eCl@ss 9.0    | 27400602 |

## DIN rail perforated - NS 35/15 ZN PERF 2000MM - 1206599

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC001285 |
| ETIM 3.0 | EC001285 |
| ETIM 4.0 | EC000212 |
| ETIM 5.0 | EC000212 |
| ETIM 6.0 | EC001285 |
| ETIM 7.0 | EC001285 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30212109 |
| UNSPSC 7.0901 | 39121708 |
| UNSPSC 11     | 39121708 |
| UNSPSC 12.01  | 39121708 |
| UNSPSC 13.2   | 39121708 |
| UNSPSC 18.0   | 39121708 |
| UNSPSC 19.0   | 39121708 |
| UNSPSC 20.0   | 39121708 |
| UNSPSC 21.0   | 39121708 |

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1206599](#)