

## Sealing cap - PROT-M 8 FS-PA-CHAIN - 1430857

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

M8 sealing cap made of plastic with fixing band for sensor cables, for M8 plugs



RoHS

### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 10 pc                                                                                                   |
| GTIN         | <br>4 046356 332866 |
| GTIN         | 4046356332866                                                                                           |

### Technical data

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -25 °C ... 85 °C |
| Degree of protection            | IP65             |
|                                 | IP67             |

#### Material

|                                        |                    |
|----------------------------------------|--------------------|
| Flammability rating according to UL 94 | V0                 |
| Material                               | PA 6.6 GF          |
| Sealing material                       | NBR                |
| Additional material specifications     | PUR (Holding band) |

#### Standards and Regulations

|                                        |    |
|----------------------------------------|----|
| Flammability rating according to UL 94 | V0 |
|----------------------------------------|----|


#### Environmental Product Compliance

|            |                                                                                                     |
|------------|-----------------------------------------------------------------------------------------------------|
| China RoHS | Environmentally Friendly Use Period = 25;                                                           |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

### Drawings

## Sealing cap - PROT-M 8 FS-PA-CHAIN - 1430857

Dimensional drawing



Dimensional drawing

### Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 23111190 |
| eCl@ss 4.0    | 27141200 |
| eCl@ss 4.1    | 27141200 |
| eCl@ss 5.0    | 27149100 |
| eCl@ss 5.1    | 27149100 |
| eCl@ss 6.0    | 27261200 |
| eCl@ss 7.0    | 27440208 |
| eCl@ss 8.0    | 23111190 |
| eCl@ss 9.0    | 23111190 |

ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC002040 |
| ETIM 4.0 | EC002040 |
| ETIM 5.0 | EC002040 |
| ETIM 6.0 | EC000032 |
| ETIM 7.0 | EC000032 |

## Sealing cap - PROT-M 8 FS-PA-CHAIN - 1430857

### Classifications

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31251501 |
| UNSPSC 7.0901 | 31251501 |
| UNSPSC 11     | 31251501 |
| UNSPSC 12.01  | 31251501 |
| UNSPSC 13.2   | 31251501 |
| UNSPSC 18.0   | 31261502 |
| UNSPSC 19.0   | 31261502 |
| UNSPSC 20.0   | 31261502 |
| UNSPSC 21.0   | 31261502 |

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1430857