

Tool - UNIFOX-PC VDE - 1212205

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Needle-nose pliers with blade, angled 45°, notched grip area, VDE 1000 V AC/1500 V DC tested

Your advantages

- ✓ The tools feature ergonomic two-component safety handles
- ✓ Individually tested safety tools according to DIN EN 60900 (VDE 0682-201)
- ✓ For working on or in the vicinity of live parts up to 1000 V AC or 1500 V DC

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 454216
GTIN	4046356454216

Technical data

Dimensions

Length (b)	170 mm
------------	--------

General

Color	black
Test standard	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5745
Weight	215 g

Standards and Regulations

Test standard	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5745

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Tool - UNIFOX-PC VDE - 1212205

Classifications

eCl@ss

eCl@ss 10.0.1	21043816
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043816
eCl@ss 8.0	21043817
eCl@ss 9.0	21043816

ETIM

ETIM 2.0	EC000142
ETIM 3.0	EC000142
ETIM 4.0	EC000833
ETIM 5.0	EC000833
ETIM 6.0	EC000835
ETIM 7.0	EC000835

UNSPSC

UNSPSC 6.01	23171604
UNSPSC 7.0901	23171604
UNSPSC 11	23171604
UNSPSC 12.01	23171604
UNSPSC 13.2	27112126
UNSPSC 19.0	27112126

Approvals

Approvals

Approvals

VDE Zeichengenehmigung / EAC / EAC

Ex Approvals

Approval details

VDE Zeichengenehmigung		http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx	109845
------------------------	---	---	--------

Tool - UNIFOX-PC VDE - 1212205

Approvals

EAC		EAC-Zulassung
-----	---	---------------

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212205](#)