

Ferrule - A 95 -40 - 3241242

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Ferrule, length: 40 mm, color: silver

Your advantages

- ✓ The ferrules without plastic sleeve are made from soft tin-plated electrolytic copper

RoHS

Key Commercial Data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 046356 908153
GTIN	4046356908153

Technical data

Dimensions

Length (b)	40 mm
Maximum stripping length	40 mm
Inner dimension of the insulating collar (d)	17 mm
Ferrule diameter	14.5 mm
Sleeve wall thickness	0.4 mm

Ambient conditions

Short-term temperature	120 °C
Max. permanent temperature	105 °C

General

Note	These ferrules are not included in DIN 46228-1: 1992-08
Color	silver
Material	CU-DHP
Coating	tin-plated (galvanic)

Ferrule - A 95 -40 - 3241242

Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27400201
eCl@ss 4.1	27060700
eCl@ss 5.0	27400200
eCl@ss 5.1	27400200
eCl@ss 6.0	27400200
eCl@ss 7.0	27400290
eCl@ss 8.0	27400201
eCl@ss 9.0	27400201

ETIM

ETIM 5.0	EC000005
ETIM 6.0	EC000005
ETIM 7.0	EC000005

UNSPSC

UNSPSC 13.2	27121703
UNSPSC 18.0	27121703
UNSPSC 19.0	27121703
UNSPSC 20.0	27121703
UNSPSC 21.0	27121703

Accessories

Accessories

Crimping tool

Crimping pliers - CRIMPFOX-C120 - 1212318



Basic pliers, for accommodating dies for a wide range of type of contacts up to 120 mm²

Die

Ferrule - A 95 -40 - 3241242

Accessories

Replacement die - CRIMPFOX-C120 AI 95/M-DIE - 1212336



Die (upper part), for CRIMPFOX-C120, for ferrules (DIN 46228) 95 mm², trapeze crimp

Replacement die - CRIMPFOX-C120 AI 95/F-DIE - 1212339



Die (lower part), for CRIMPFOX-C120, for ferrules (DIN 46228) 95 mm², trapeze crimp

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

3241242