

Tool bag, equipped - TOOL-CARRIER - 1212503

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Tool bag, equipped with: cable cutter, diagonal cutter, stripping pliers, NYM stripping tool, stripping tool for removing sheath, crimping pliers, crimping die for ferrules, combination, needle-nose, and water pump pliers, VDE screwdriver, bladed: 0.4 x 2.5/0.5 x 3.0/1.0 x 4.0/1.0 x 6.5, Philips: PHO/PH1/PH2, voltage tester, control cabinet key, knife, tape measure

Your advantages

- ✓ Rugged and heavy-duty tool bags
- ✓ Universal tool sets, with cutting, stripping, crimping, and testing tools from the TOOL fox tool range

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 528399
GTIN	4046356528399

Technical data

Dimensions

Length (b)	290 mm
Width (a)	185 mm
Height (c)	220 mm

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Articles in set

Diagonal cutter - CUTFOX-S VDE - 1212207



Diagonal cutter for hard (piano wire) and soft wires, VDE 1000 V AC/1500 V DC tested

Tool bag, equipped - TOOL-CARRIER - 1212503

Articles in set

Cable-cutting tool - CUTFOX 18 - 1212129



Cable cutter, angled, for copper and aluminum up to 18 mm diameter (up to 50 mm²)

Stripping tool - WIREFOX 10 VDE - 1212366



Stripping pliers, for removing the sheath from cables up to 5 mm in diameter, for stripping conductors with a cross section of up to 10 mm², scale for measuring the stripping length; VDE-tested.

Stripping tool - WIREFOX-D 13 - 1212162



Stripping tool, for stripping installation lines of Ø 8 - 13 mm, e.g. NYM 3 x 1.5 mm² to 5 x 2.5 mm², single line stripping 0.2 mm² - 4 mm², with longitudinal cut blade and sliding knife

Stripping tool - WIREFOX-D 28 - 1212174



Stripping tool, for stripping lines of Ø 8 - 28 mm

Crimping pliers - CRIMPFOX-M - 1212072



Basic pliers, for accommodating dies for a wide range of type of contacts

Tool bag, equipped - TOOL-CARRIER - 1212503

Articles in set

Replacement die - CRIMPFOX-M 10/DIE - 1212080



Die, for Crimpfox-M, for ferrules 0.25 - 10 mm², packed in a serial storage box

Tool - UNIFOX-CE VDE - 1212203



Combination pliers, angled design, with opening spring and locking device, cross-notched grip area, integrated M8 - M10 ring wrench, VDE 1000 V AC/1500 V DC tested

Tool - UNIFOX-P VDE - 1212204



Needle-nose pliers with blade, notched grip area, VDE 1000 V AC/1500 V DC tested

Tool - UNIFOX-WP - 1212365



Water pump pliers, with groove joint, grip areas with dual notching, acc. to VDE ISO 8976

Screwdriver - SZS 0,4X2,5 VDE - 1205037



Screwdriver, slot-headed, VDE insulated, size: 0.4 x 2.5 x 80 mm, 2-component grip, with non-slip grip

Tool bag, equipped - TOOL-CARRIER - 1212503

Articles in set

Screwdriver - SZS 0,5X3,0 VDE - 1207404



Screwdriver, slot-headed, VDE insulated, size: 0.5 x 3.0 x 100 mm, 2-component grip, with non-slip grip

Screwdriver - SZS 1,0X4,0 VDE - 1205066



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 4.0 x 100 mm, 2-component grip, with non-slip grip

Screwdriver - SZS 1,0X6,5 VDE - 1205079



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 6.5 x 150 mm, 2-component grip, with non-slip grip

Screwdriver - SZK PH0 VDE - 1205147



Screwdriver, PH crosshead, VDE insulated, size: PH 0 x 80 mm, 2-component grip, with non-slip grip

Screwdriver - SZK PH1 VDE - 1205150



Screwdriver, PH crosshead, VDE insulated, size: PH 1 x 80 mm, 2-component grip, with non-slip grip

Tool bag, equipped - TOOL-CARRIER - 1212503

Articles in set

Screwdriver - SZK PH2 VDE - 1205163



Screwdriver, PH crosshead, VDE insulated, size: PH 2 x 100 mm, 2-component grip, with non-slip grip

Voltage tester - DUSPOL EXPERT - 1209091



Voltage tester, for DC and AC voltages from 12 V to 1000 V AC/1000 V DC, IP65

Control cabinet key - USS 4 - 1203149



Control cabinet key, metal, for all common types of control cabinet

Tool bag, unequipped - TOOL-CARRIER EMPTY - 1212499



Tool bag, unequipped

Measuring instrument - MEASURING TAPE 5M I/M - 1200304



Measuring tape with automatic tape feed and locking mechanism, measuring rail: imperial/metric, length: 5 m

Classifications

eCl@ss

eCl@ss 10.0.1	21045003
eCl@ss 4.0	21043000

Tool bag, equipped - TOOL-CARRIER - 1212503

Classifications

eCl@ss

eCl@ss 4.1	21043000
eCl@ss 5.0	21049000
eCl@ss 5.1	21049000
eCl@ss 6.0	21049000
eCl@ss 7.0	21045003
eCl@ss 8.0	21045003
eCl@ss 9.0	21045003

ETIM

ETIM 3.0	EC000149
ETIM 4.0	EC000149
ETIM 5.0	EC000149
ETIM 6.0	EC000149
ETIM 7.0	EC000149

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	27113201
UNSPSC 18.0	27113201
UNSPSC 19.0	27113201
UNSPSC 20.0	27113201
UNSPSC 21.0	27113201

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01750
-----	---	--------------------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212503](#)