

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Ferrule, Sleeve length: 8 mm, Length: 14 mm, Color: red

The illustration shows the versions A 1-8 and A 1-10, in red

Product Features

- The Al 0,25.. ferrules can also be used to process 0.14 mm² conductors
- The ferrules with plastic sleeve are made from soft tin-plated electrolytic copper
- The insulation reliability of close connections is increased and the splicing of wires is prevented



Key Commercial Data

| Packing unit | 1 pc |
|--------------------------------------|-----------------|
| Minimum order quantity | 100 pc |
| GTIN | 4 017918 093686 |
| Weight per Piece (excluding packing) | 0.104 g |
| Custom tariff number | 85369010 |
| Country of origin | Germany |

Technical data

Dimensions

| Length (b) | 14 mm |
|--|--------|
| Maximum stripping length | 11 mm |
| Sleeve length | 8 mm |
| Inner dimension of the insulating collar (d) | 3 mm |
| Ferrule diameter | 1.5 mm |
| Insulating collar thickness | 0.3 mm |



Technical data

Dimensions

| Sleeve wall thickness | 0.15 mm |
|-----------------------|---------|
| Ambient conditions | |

| Short-term temperature | 120 °C |
|----------------------------|--------|
| Max. permanent temperature | 105 °C |

General

| Color | red |
|--|--------------------------------|
| Components | free from silicone and halogen |
| Flammability rating according to UL 94 | НВ |
| Material | E-CU |
| Coating | tin-plated (galvanic) |

Standards and Regulations

| Connection in acc. with standard | CSA |
|--|-----|
| Flammability rating according to UL 94 | НВ |

Classifications

eCl@ss

| eCl@ss 4.0 | 27060701 |
|------------|----------|
| eCl@ss 4.1 | 27060701 |
| eCl@ss 5.0 | 27400201 |
| eCl@ss 5.1 | 27400201 |
| eCl@ss 6.0 | 27400201 |
| eCl@ss 7.0 | 27400201 |
| eCl@ss 8.0 | 27400201 |

ETIM

| ETIM 2.0 | EC000005 |
|----------|----------|
| ETIM 3.0 | EC000005 |
| ETIM 4.0 | EC000005 |
| ETIM 5.0 | EC000005 |

UNSPSC

| UNSPSC 6.01 | 30212109 |
|---------------|----------|
| UNSPSC 7.0901 | 27121703 |
| UNSPSC 11 | 27121703 |
| UNSPSC 12.01 | 27121703 |




Classifications

| UNSPSC | | |
|----------------------------------|----------|--|
| UNSPSC 13.2 | 27121703 | |
| Approvals | | |
| Approvals | | |
| Approvals | | |
| CSA / CSAus / EAC / EAC / cCSAus | | |
| Ex Approvals | | |
| Approvals submitted | | |
| Approval details | | |
| CSA ® | | |
| CSAus | | |
| EAC | | |
| EAC | | |
| cCSAus | | |

Drawings



Dimensional drawing



Phoenix Contact 2016 © - all rights reserved http://www.phoenixcontact.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact: 3200030