

Crimping pliers - CRIMPFOX-HS 6 - 1212722

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for fully insulated shrink connectors, 0.5 ... 6.0 mm² (red, blue, yellow), oval crimp

Your advantages

- ✓ Crimping pliers for cable lugs and connectors
- ✓ They unlock as soon as the required crimping pressure is reached, therefore ensuring sufficient pressure is applied.
- ✓ The color-coded dies clearly indicate the cross section.
- ✓ Unlockable pressure lock



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 857819
GTIN	4046356857819

Technical data

Dimensions

Length (b)	256 mm
Width (a)	22 mm
Height (c)	80 mm

General

Color	black
Compression	Oval crimp
Type of contact	Fully insulated shrink connectors
Designation	Crimping position 1
Min. cross section	0.5 mm ²
Max. cross section	1.5 mm ²
AWG min	20
AWG max	16
Designation	Crimping position 2
Min. cross section	1.5 mm ²

Crimping pliers - CRIMPFOX-HS 6 - 1212722

Technical data

General

Max. cross section	2.5 mm ²
AWG min	16
AWG max	14
Designation	Crimping position 3
Min. cross section	4 mm ²
Max. cross section	6 mm ²
AWG min	12
AWG max	10
Weight	550 g
Min. cross section	0.5 mm ²
Max. cross section	6 mm ²

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC000168
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	27111518

Crimping pliers - CRIMPFOX-HS 6 - 1212722

Classifications

UNSPSC

UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212722](#)