

Front adapters - FLKM S135-465-4UA/UI/S400 - 2314888

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



The FLKM S135/S400 adapter links a SIMATIC® S5 plug directly with the basic SIMATIC® S7 400 card.
Conversion: 6ES5 465-4UA13 (Pt 100) on 6ES7 431 0HH0-0AB0 / 6ES7 431 7QH00-0AB0

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 155342
GTIN	4046356155342

Technical data

Note

Type of note	Notes on operation
Note	The LEDs of the S7-400 module are hidden.

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. permissible operating voltage	60 V DC
Max. permissible current	4 A (per path) 4 A (per connection, supply via separate power supply)
Mounting position	any
Degree of protection	IP00

Connection data 1

Connection name	Field level
Connection method	SIEMENS S5-135 U pin strip

Supported controller

Controller	SIEMENS S5-135 U
------------	------------------

Front adapters - FLKM S135-465-4UA/UI/S400 - 2314888

Technical data

Supported controller

- suitable I/O card	6ES5 465-4UA13
---------------------	----------------

Standards and Regulations


Standards/regulations	IEC 60664
	DIN EN 50178
Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (Functional insulation)
Degree of pollution	2
Overvoltage category	II

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Circuit diagram



FLKM S135-465-4UA/UI/S400 connection scheme

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.A*30.B.01742
-----	---	--------------------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2314888