

## Adapter plate - HC-B24/16-ADP-SS - 1034216

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Adapter plate, type: B24 to B16

COMPLETE SW

### Key Commercial Data

|              |                                                                                                        |
|--------------|--------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                                   |
| GTIN         | <br>4 055626 540627 |
| GTIN         | 4055626540627                                                                                          |

### Technical data

#### Dimensions

|                                 |        |
|---------------------------------|--------|
| Length                          | 151 mm |
| Height                          | 5 mm   |
| Hole diameter                   | 5.5 mm |
| Width                           | 53 mm  |
| Drill hole distance, horizontal | 130 mm |
| Drill hole distance, vertical   | 32 mm  |

#### General

|                       |                                          |
|-----------------------|------------------------------------------|
| Note                  | For wall cutouts of type B24             |
| Material              | Stainless steel 1.4301/AISI 304          |
| Type                  | B24                                      |
| Assembly instructions | Torque of the mounting screws 1 ... 2 Nm |


#### Environmental Product Compliance

|            |                                                                                                     |
|------------|-----------------------------------------------------------------------------------------------------|
| China RoHS | Environmentally Friendly Use Period = 50 years                                                      |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

### Drawings

## Adapter plate - HC-B24/16-ADP-SS - 1034216

Dimensional drawing



Dimensional drawing

### Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27440201 |
| eCl@ss 6.0    | 27261200 |
| eCl@ss 7.0    | 27440201 |
| eCl@ss 9.0    | 27440201 |

ETIM

|          |          |
|----------|----------|
| ETIM 5.0 | EC002309 |
| ETIM 6.0 | EC002309 |
| ETIM 7.0 | EC002309 |

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1034216](#)