

## Reducing adapter - REDUC-M-KV-M20/M16 - 1647611

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Reducing adapter, material: Brass, nickel-plated, connecting thread: M20 x 1.5, color: silver, with O-ring

### Product Description

Reduced M20 to M16

RoHS

### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 10 pc                                                                                                   |
| Minimum order quantity | 10 pc                                                                                                   |
| GTIN                   | <br>4 017918 941512 |
| GTIN                   | 4017918941512                                                                                           |

### Technical data

#### Dimensions

|                                  |        |
|----------------------------------|--------|
| Length                           | 9 mm   |
| Length without connecting thread | 2.5 mm |
| Connecting thread diameter       | 20 mm  |
| Hexagon angular dimension        | 24 mm  |
| Length of the connecting thread  | 6.5 mm |

#### Ambient conditions

|                                 |                                             |
|---------------------------------|---------------------------------------------|
| Degree of protection (IP)       | IP65 (Depends on the screw connection used) |
| Ambient temperature (operation) | -20 °C ... 80 °C                            |

#### General

|                 |                      |
|-----------------|----------------------|
| Material        | Brass, nickel-plated |
| Outer thread    | M20                  |
| Internal thread | M16                  |
| Torque          | 2.5 Nm ... 2.7 Nm    |
| Color           | silver               |

## Reducing adapter - REDUC-M-KV-M20/M16 - 1647611

### Technical data

#### Standards and Regulations


|              |    |
|--------------|----|
| Halogen-free | no |
|--------------|----|

#### Environmental Product Compliance

|            |                                                                                                     |
|------------|-----------------------------------------------------------------------------------------------------|
| REACH SVHC | Lead 7439-92-1                                                                                      |
| China RoHS | Environmentally Friendly Use Period = 50 years                                                      |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

### Drawings

Dimensional drawing



Dimensional drawing

## Reducing adapter - REDUC-M-KV-M20/M16 - 1647611

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27440201 |
| eCl@ss 4.0    | 27141200 |
| eCl@ss 4.1    | 27141200 |
| eCl@ss 5.0    | 27149100 |
| eCl@ss 5.1    | 27149100 |
| eCl@ss 6.0    | 27149100 |
| eCl@ss 7.0    | 27439207 |
| eCl@ss 8.0    | 27149109 |
| eCl@ss 9.0    | 27440201 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000441 |
| ETIM 3.0 | EC000441 |
| ETIM 4.0 | EC000441 |
| ETIM 5.0 | EC000938 |
| ETIM 6.0 | EC002309 |
| ETIM 7.0 | EC002309 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211808 |
| UNSPSC 7.0901 | 39121408 |
| UNSPSC 11     | 39121408 |
| UNSPSC 12.01  | 39121408 |
| UNSPSC 13.2   | 39121408 |
| UNSPSC 18.0   | 31261501 |
| UNSPSC 19.0   | 31261501 |
| UNSPSC 20.0   | 31261501 |
| UNSPSC 21.0   | 31261501 |

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1647611](#)