

Housing cover - ME-IO 18,8 C 2U MC 7035 - 2202616

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail housing, 2U for marking lid, Housing cover, width: 18.9 mm, height: 21.9 mm, depth: 26 mm, color: light gray (7035)

Your advantages

- ✓ Plastic in accordance with UL94 V0: for more rigorous flammability requirements
- ✓ Cover for fully closed device fronts
- ✓ Enables the use of a transparent marking cover



Key Commercial Data

Packing unit	30 pc
Minimum order quantity	30 pc
GTIN	 4 055626 210490
GTIN	4055626210490

Technical data

Item properties

Brief article description	Housing cover
Type	ME-IO 18,8 C 2U MC 7035
Order No.	2202616
Housing type	DIN rail housing
Type	2U for marking lid
Max. IP code to attain	IP20
Mounting type	Snap in

Dimensions

Width [w]	18.9 mm
Height [h]	21.9 mm
Depth [d]	26 mm

Housing cover - ME-IO 18,8 C 2U MC 7035 - 2202616

Technical data

Material data

Housing material	Polyamide
Color (RAL)	light gray (7035)
Flammability rating according to UL 94	V0

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Relative humidity (storage/transport)	80 %

PCB data

Mounting position	Vertical (horizontal DIN rail)
-------------------	--------------------------------

Packaging information

Type of packaging	packed in cardboard
Pieces per package	30
Denomination packing units	Pcs.
Outer packaging type	Carton

Standards and regulations

Flammability rating according to UL 94	V0
--	----


Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Housing cover - ME-IO 18,8 C 2U MC 7035 - 2202616

Schematic diagram



Classifications

eCl@ss

eCl@ss 10.0.1	27182702
eCl@ss 5.0	27371300
eCl@ss 5.1	27371300
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
----------	----------

Housing cover - ME-IO 18,8 C 2U MC 7035 - 2202616

Classifications

ETIM

ETIM 6.0	EC001031
ETIM 7.0	EC001031

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01687
-----	---	---------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2202616](#)