

Membrane keypad - KP HCS T-MIN K21 C3 P14 - 2203569

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Membrane keypad, self-adhesive, silver conduction technology, 21 keys, embossed, 3 colors, connection cable: 59 mm, with crimp female connector RM 2.54 mm, operating temperature -20 °C ... 70 °C

Your advantages

- ✓ Easy integration into electronics housings of the HCS and DCS series
- ✓ Membrane keypads in various sizes and colors for customized device designs
- ✓ Customer-specific key layouts on request



Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 474021
GTIN	4055626474021

Technical data

Product properties

Type	KP HCS T-MIN K21 C3 P14
Order No.	2203569
Mounting type	adhesive
Number of positions	14
Number of keys	21 (3 x 7)
Number of socket pins	14
Technology	Conductive silver technology
Embossing	Dome embossing 11 x 11 mm

Dimensions

Dimensions	78 mm x 173 mm
	55 mm x 173 mm
	128 mm x 64 mm (LCD cutout)
Pitch	2.54 mm

Membrane keypad - KP HCS T-MIN K21 C3 P14 - 2203569

Technical data

Dimensions

Length	59 mm (Membrane cable)
--------	------------------------

Ambient conditions

Ambient temperature (storage/transport)	-20 °C ... 70 °C
Ambient temperature (operation)	-40 °C ... 80 °C

Packaging details

Pieces per package	1
Denomination packing units	Pcs.

Classifications

eCl@ss

eCl@ss 10.0.1	27182702
eCl@ss 5.1	27180506
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

Accessories

Additional products

Electronic housing - HCS-T MINI 1W C C C 7035 - 2203131



Handheld housing, T-Mini, light gray, consisting of two half shells with screws, front 1.1 mm recessed, with window and keypad slot

Electronic housing - HCS-T MINI 1W 3AA C C 7035 - 2203134



Handheld housing, T-Mini, light gray, consisting of two half shells with screws. Front 1.1 mm recessed, with window and keypad slot, battery compartment cover and battery contacts for 3 AA batteries

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2203569](#)