

Membrane keypad - KP HCS T-MAX K45 C4 P16 - 2203571

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Membrane keypad, self-adhesive, silver conduction technology, 45 keys, embossed, 4 colors, connection cable: 77 mm, with crimp female connector RM 2.54 mm, operating temperature -20 °C ... 70 °C

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 528670
GTIN	4055626528670

Technical data

Product properties

Type	KP HCS T-MAX K45 C4 P16
Order No.	2203571
Mounting type	adhesive
Number of positions	16
Number of keys	45 (9 x 5)
Number of socket pins	16
Technology	Conductive silver technology
Embossing	Dome embossing 11 x 11 mm

Dimensions

Dimensions	144 mm x 78 mm
Pitch	2.54 mm
Length	77 mm (Membrane cable)

Ambient conditions

Ambient temperature (storage/transport)	-20 °C ... 70 °C
Ambient temperature (operation)	-40 °C ... 80 °C

Packaging details

Membrane keypad - KP HCS T-MAX K45 C4 P16 - 2203571

Technical data

Packaging details

Pieces per package	1
Denomination packing units	Pcs.

Classifications

eCl@ss

eCl@ss 10.0.1	27182702
eCl@ss 5.1	27180506
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

Accessories

Additional products

Electronic housing - HCS-T MAXI 1W C C C 7035 - 2203142



Handheld housing, T-Maxi, light gray, consisting of two half shells with screws, front 1.1 mm recessed, with window and keypad slot

Electronic housing - HCS-T MAXI 1W C 1 1 7035 - 2203143



Handheld housing, T-Maxi, light gray, consisting of two half shells, two front plates with screws, front 1.1 mm recessed, with window and keypad slot

Electronic housing - HCS-T MAXI 1W 5AA 1 1 7035 - 2203144



Handheld housing T-Maxi light gray, comprising two half shells, two front lenses, screws. Front 1.1 mm recessed, with window and keyboard slot Battery compartment cover and battery contacts, for 5 AA batteries

Membrane keypad - KP HCS T-MAX K45 C4 P16 - 2203571

Accessories

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2203571](#)