

Module carrier frame - HC-M-D15-MF-HB - 1062122

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid
(<http://phoenixcontact.com/download>)

Module carrier frame, size: D15, 0.14 mm² ... 2.5 mm², application: Module carrier frame, for size D15 housings



Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 718040
GTIN	4055626718040

Technical data

Dimensions

Height	36 mm
Width	23 mm
Length	56.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Mechanical characteristics

Conductor cross section	0.14 mm ² ... 2.5 mm ² (applies to stranded conductors with ferrules)
Connection cross section AWG	24 ... 14
Insertion/withdrawal cycles	≥ 500

General

Note	for modular contact inserts with a width of 14.6 mm in conjunction with size D15 housings.
Size	D15
Number of module slots	1
Assembly instructions	Maximum allowable conductor cross section for the modules used: 2.5 mm ²

Material data

Module carrier frame - HC-M-D15-MF-HB - 1062122

Technical data

Material data


Contact surface material	Nickel
Contact carrier material	Die-cast zinc alloy

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Dimensional drawing



Dimensional drawing

Module carrier frame - HC-M-D15-MF-HB - 1062122

Classifications

eCl@ss

eCl@ss 10.0.1	27440206
eCl@ss 6.0	27261200
eCl@ss 7.0	27440206
eCl@ss 9.0	27440206

ETIM

ETIM 6.0	EC002312
ETIM 7.0	EC002312

Accessories

Accessories

Coding element

Coding element - HC-CST-MOD - 1636127



Coding peg for coding up to 16 connectors, for HC Modular

Coding element - HC-CBU-MOD - 1636130



Coding socket for coding up to 16 connectors, for HC Modular

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1062122