

## Connecting cable - PRC 5-CA-F-H07-4-2,5 - 1150675

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Circular connectors (cable-side), Range of articles: PRC, Connecting cable, housing material: PPE, color: black, number of positions: 5, nom. voltage: 690 V AC, rated current: 32 A, Connection method: Screw connection, Type of contact: Socket

### Your advantages

- ✓ Time savings of 80% for startup with Plug and Play
- ✓ Locking mechanism can be unlocked manually or using a tool
- ✓ Suitable for applications in atmospheres containing salt and in direct sunlight
- ✓ Ideal for indoor and outdoor use due to weatherproof materials



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 147877
GTIN	4063151147877

### Technical data

#### General data

Number of positions	5
Color	black
Width	37.6 mm
Height	37.6 mm
Length	2.5 m

#### Connection data

Rated current	32 A
Nominal voltage ATD	690 V AC
Rated voltage (III/2)	690 V
Type of contact	Socket
Connection method	Screw connection
Insulating material group	I / CTI 600

# Connecting cable - PRC 5-CA-F-H07-4-2,5 - 1150675

## Technical data

### Material data

Contact material	Cu
Contact surface material	silver-plated
Contact carrier material	PPE
Housing material	PPE
Seal material	EPDM
O-ring material	EPDM
Cable gland material	PPE
Color of the housing part	black
Knurl material	PPE

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

## Classifications

eCl@ss

eCl@ss 10.0.1	27440109
eCl@ss 9.0	27440103

## Accessories

### Accessories

Circular connector (cable-side)

Distributor - PRC ED-T 115/205-4-HR-GN - 1079659



Circular connectors (cable-side), Range of articles: PRC, Distributor, housing material: Polycarbonate fiber reinforced, color: black, nom. voltage: 400 V, rated current: 32 A, Connection method: pre-assembled, Type of contact: Input: pin / outputs: socket

Distributor - PRC ED-H 115/305-4-HR-GN - 1079660



Circular connectors (cable-side), Range of articles: PRC, Distributor, housing material: Polycarbonate fiber reinforced, color: black, nom. voltage: 400 V, rated current: 32 A, Connection method: pre-assembled, Type of contact: Input: pin / outputs: socket

## Connecting cable - PRC 5-CA-F-H07-4-2,5 - 1150675

### Accessories

Distributor - PRC ED-H 115/303-4-HR-GN - 1079661



Circular connectors (cable-side), Range of articles: PRC, Distributor, housing material: Polycarbonate fiber reinforced, color: black, nom. voltage: 400 V, rated current: 32 A, Connection method: pre-assembled, Type of contact: Input: pin / outputs: socket

---

### Protective cover

Protective cap - PRC COVER F - 1409236



Protective cover, Range of articles: PRC, Protective cap, housing material: PPE, color: black. Suitable for couplings (FS)

---

Protective cap - PRC COVER M - 1409237



Protective cover, Range of articles: PRC, Protective cap, housing material: PPE, color: black. Suitable for connectors (MS)

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

**PHOENIX CONTACT GmbH & Co. KG**  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1150675