

Power module - EMD-SL-PS45-110AC - 2885281

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Power modules, pluggable, for EMD-FL-..., supply voltage: 88 V AC ... 121 V AC

Your advantages

- ✓ Variable supply voltage range
- ✓ Adjustable asymmetry
- ✓ Adjustable via potentiometer on the front
- ✓ Adjustable response delay

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 996529
GTIN	4017918996529

Technical data

Dimensions

Width	32 mm
Height	35 mm
Depth	26 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C

Input data

Nominal input voltage	110 V AC (50/60 Hz)
-----------------------	---------------------

General

Housing material	Plastic
------------------	---------

Environmental Product Compliance

Power module - EMD-SL-PS45-110AC - 2885281

Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 5.0	27049002
eCl@ss 5.1	27049200
eCl@ss 6.0	27049000
eCl@ss 7.0	27049002
eCl@ss 8.0	27049002
eCl@ss 9.0	27040701

ETIM

ETIM 4.0	EC002540
ETIM 5.0	EC002540
ETIM 6.0	EC002540
ETIM 7.0	EC002540

UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121535
UNSPSC 11	39121535
UNSPSC 12.01	39121535
UNSPSC 13.2	39121004
UNSPSC 19.0	39121004

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

Power module - EMD-SL-PS45-110AC - 2885281

Approvals

EAC



RU *-
DE.**08.B-02133

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2885281](#)