

FO connectors - VS-PPC-C1-SCRJ-POBK-PG9-A3C-C - 1657863

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid
(<http://phoenixcontact.com/download>)



SC-RJ fiber optic connector, IP67, with push-pull interlocking, plastic housing, duplex, with fast connection technology, for PCF fiber 200/230 µm, for individual wire diameter 2.2 mm, for cable cross section 6.5 mm ... 9.5 mm



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 131933
GTIN	4046356131933

Technical data

Mechanical characteristics

Minimum external conductor diameter	6.5 mm
Maximum external conductor diameter	9.5 mm
Degree of pollution	2
Locking type	Push Pull
Weight	34.24 g
Flammability rating according to UL 94	V0

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
---------------------------------	------------------

Material data

Housing material	PA-GF
Width	22 mm
Height	30 mm
Length	62.5 mm

Electrical characteristics

Number of positions	2
Degree of pollution	2

FO connectors - VS-PPC-C1-SCRJ-POBK-PG9-A3C-C - 1657863

Technical data

Electrical characteristics

Attenuation	< 1 dB (Insertion attenuation)
-------------	--------------------------------

Standards and Regulations


Standards/specifications	IEC PAS 61076-3-117
Flammability rating according to UL 94	V0

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings


Dimensional drawing



Push-Pull SC-RJ connector IP65/67

FO connectors - VS-PPC-C1-SCRJ-POBK-PG9-A3C-C - 1657863

Schematic diagram



Classifications

eCl@ss

eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440312
eCl@ss 8.0	19170122
eCl@ss 9.0	19170122

ETIM

ETIM 3.0	EC001122
ETIM 4.0	EC001122
ETIM 5.0	EC001122
ETIM 6.0	EC001122
ETIM 7.0	EC001122

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501

FO connectors - VS-PPC-C1-SCRJ-POBK-PG9-A3C-C - 1657863

Classifications

UNSPSC

UNSPSC 12.01	31261501
UNSPSC 13.2	43223310
UNSPSC 18.0	43223310
UNSPSC 19.0	43223310
UNSPSC 20.0	43223310
UNSPSC 21.0	43223310

Accessories

Accessories

Data plug

Assembly tool - PSM-HCS-KONFTOOL/SC-RJ - 2708876



HCS assembly kit for SC-RJ quick mounting connectors, including stripping blade, stripping pliers, aramide yarn scissors, fiber stripper, microscope, fiber cleaving tool for standard HCS and HCS GI fibers, two SC-RJ connectors for standard HCS fiber, and documentation

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1657863