

Software - VISU+ 2 RT 512 WEB1 NETWORK - 2988081

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Runtime license for Visu+ including 1 web client and networking function where the I/O data and variables in scripting are limited to 512 bytes.

Your advantages

- ✓ Full SCADA (Supervisory Control And Data Acquisition) function with visualization, trend representation, and alarm management
- ✓ Data logging, trend display, and recipe management
- ✓ Scripts can be created in VBA and IL
- ✓ Control coupling with OPC
- ✓ Fully scalable process diagrams for using one design on different devices and monitor sizes
- ✓ Multilingual software and projects, thanks to Unicode support and online selection
- ✓ Access protection with user management



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 566452
GTIN	4046356566452

Technical data

License information

Intended use for the software	Visualization
Type of license	Runtime license

Functions

Basic functions	Know-How protection and safety through encoding of projects
	Realtime database coupling with ODBC to MS ACCESS, MS EXCEL and SQL server
	FDA CFR 21 Part 11 compatible
Expanded functionality	Web client capability
	Networking

Software - VISU+ 2 RT 512 WEB1 NETWORK - 2988081

Technical data

Functions

Integrated function	Web client
	Networking
	Online configuration
	Password protection
	Language selection
Number of I/O nodes	512 I/O bytes

Hardware requirements

Hard disk	min. 1 GByte (recommended: 2 GB)
RAM	min. 1 GByte (2 GB for Windows Vista and Windows 7)
CPU	Pentium/Celeron, 1.6 GHz
Optical drive	DVD-ROM
Screen resolution	rec. 1024 pixel(s) x 768 pixel(s) (XGA)
Operating equipment	Keyboard, mouse

Software requirements

Operating system	Windows® XP (SP3)
	Windows® Vista Business
	Windows® 7 Professional SP1 (32-Bit/64-Bit)
	Windows® 7 Ultimate SP1 (32-Bit/64-Bit)
	Windows® 8 Professional (32-Bit/64-Bit)
	Windows® 8 Enterprise (32-Bit/64-Bit)
	Windows® Server 2003
	Windows® Server 2008
	Windows® Server 2008 R2
	Windows® 10 (32-Bit/64-Bit)
Languages supported	German, English, French, Italian
Supported browsers	Internet Explorer 5.5 or higher

Classifications

eCl@ss

eCl@ss 10.0.1	27242502
eCl@ss 4.0	27338000
eCl@ss 4.1	27338000
eCl@ss 5.0	27242500
eCl@ss 5.1	27242500
eCl@ss 6.0	27242500
eCl@ss 7.0	27242502
eCl@ss 8.0	27242502

Software - VISU+ 2 RT 512 WEB1 NETWORK - 2988081

Classifications

eCl@ss

eCl@ss 9.0	27242502
------------	----------

ETIM

ETIM 2.0	EC001416
ETIM 3.0	EC001416
ETIM 4.0	EC001416
ETIM 5.0	EC001416
ETIM 6.0	EC001416
ETIM 7.0	EC001416

UNSPSC

UNSPSC 6.01	43163005
UNSPSC 7.0901	43232404
UNSPSC 11	43163005
UNSPSC 12.01	43232404
UNSPSC 13.2	43231507
UNSPSC 18.0	43231507
UNSPSC 19.0	43231507
UNSPSC 20.0	43231507
UNSPSC 21.0	43231507

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2988081](#)