

## Plug-in bridge - FBS 2-5 GY - 3038969

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Plug-in bridge, pitch: 5.2 mm, number of positions: 2, color: gray

### Your advantages

- ✓ The 2- to 50-pos. jumpers can bridge up to 50 terminal blocks in the two bridge shafts of the CLIPLINE complete system in one step

RoHS

COMPLETE SET

### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 50 pc                                                                                                   |
| Minimum order quantity | 50 pc                                                                                                   |
| GTIN                   | <br>4 017918 888299 |
| GTIN                   | 4017918888299                                                                                           |

### Technical data

#### Technical data

|                                        |                                                                                                                                                                                                           |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Color                                  | gray                                                                                                                                                                                                      |
| Material                               | Copper                                                                                                                                                                                                    |
| Number of positions                    | 2                                                                                                                                                                                                         |
| Pitch                                  | 5.2 mm                                                                                                                                                                                                    |
| Flammability rating according to UL 94 | V0                                                                                                                                                                                                        |
| Maximum load current                   | 24 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.) |

### Standards and Regulations

|                                        |    |
|----------------------------------------|----|
| Flammability rating according to UL 94 | V0 |
|----------------------------------------|----|

### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

## Plug-in bridge - FBS 2-5 GY - 3038969

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27141140 |
| eCl@ss 4.0    | 27141100 |
| eCl@ss 4.1    | 27141100 |
| eCl@ss 5.0    | 27141100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27141100 |
| eCl@ss 7.0    | 27141140 |
| eCl@ss 8.0    | 27141140 |
| eCl@ss 9.0    | 27141140 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000489 |
| ETIM 3.0 | EC000489 |
| ETIM 4.0 | EC000489 |
| ETIM 5.0 | EC000489 |
| ETIM 6.0 | EC000489 |
| ETIM 7.0 | EC000489 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211829 |
| UNSPSC 7.0901 | 39121426 |
| UNSPSC 11     | 39121426 |
| UNSPSC 12.01  | 39121426 |
| UNSPSC 13.2   | 39121426 |
| UNSPSC 18.0   | 39121426 |
| UNSPSC 19.0   | 39121426 |
| UNSPSC 20.0   | 39121426 |
| UNSPSC 21.0   | 39121426 |

### Approvals

#### Approvals

---

Approvals

EAC / EAC

---

Ex Approvals

---

#### Approval details

## Plug-in bridge - FBS 2-5 GY - 3038969

### Approvals

|     |                                                                                   |               |
|-----|-----------------------------------------------------------------------------------|---------------|
| EAC |  | EAC-Zulassung |
|-----|-----------------------------------------------------------------------------------|---------------|

|     |                                                                                   |                          |
|-----|-----------------------------------------------------------------------------------|--------------------------|
| EAC |  | RU C-<br>DE.A*30.B.01742 |
|-----|-----------------------------------------------------------------------------------|--------------------------|

### Accessories

#### Accessories

#### Protective cap

Protective cap - FBSC - 3012325



Covering hood, provides reliable shock protection when using cut-to-length FBS ...-5 and FBS ...-6 bridges, color: red

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3038969](#)