

Housing set - BC 107,6 DEV-KIT KMGY - 2202525

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DEV-KIT BC 107,6: contains 1 x BC 107,6 housing and PCB terminal blocks (MKDS), supplied in individual parts

Your advantages

- ✓ Standard-compliant housing according to DIN 43880 with overall width of 107,6 mm
- ✓ PCB terminal blocks with 5 mm pitch, conductor cross section 1.5 mm²
- ✓ Optional perfboard for soldering THT components by hand
- ✓ Connection of individual housing modules with each other by means of the optional HBUS via DIN rail



Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 141756
GTIN	4055626141756

Technical data

Item properties

Brief article description	Housing set
Type	BC 107,6 DEV-KIT KMGY
Order No.	2202525
Housing type	DIN rail housing for use in distribution boards in accordance with DIN 43880
Housing series	BC
Max. IP code to attain	IP20
Mounting type	Snap in

Dimensions

Width [w]	107.6 mm
Length [l]	89.7 mm

Material data

Housing set - BC 107,6 DEV-KIT KMGY - 2202525

Technical data

Material data

Housing material	Polycarbonate
Color (RAL)	light gray (7035)
Flammability rating according to UL 94	V0

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

PCB data

Mounting position	parallel to the DIN rail
Type of PCB mount	Latching

Packaging information

Pieces per package	1
Denomination packing units	Pcs.

Standards and regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	27182702
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

Housing set - BC 107,6 DEV-KIT KMGY - 2202525

Classifications

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01687
-----	---	---------

Accessories

Additional products

PCB - BC 107,6/40 U11 HBUS DEV-PCB - 2202544



Printed-circuit board for the BC 107,6 DEV-KIT

Housing set - BC 107,6 DEV-KIT KMGY - 2202525

Accessories

Plug - HBUS 107,6-16P-1S DEV-KIT BK - 2202545

Bus connector to connect BC modules on the DIN rail; suitable for BC DEV-KITS, contains HBUS 107,6 and pin strip



Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2202525](#)