

Membrane keypad - KP HCS C-MIN-P K12 C3 P9 - 2203566

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Membrane keypad, self-adhesive, silver conduction technology, 12 keys, embossed, 3 colors, connection cable: 100.5 mm, with crimp female connector RM 2.54 mm, operating temperature -20 °C ... 70 °C

Your advantages

- ✓ Easy integration into electronics housings of the HCS and DCS series
- ✓ Membrane keypads in various sizes and colors for customized device designs
- ✓ Customer-specific key layouts on request

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 472492
GTIN	4055626472492

Technical data

Product properties

Type	KP HCS C-MIN-P K12 C3 P9
Order No.	2203566
Mounting type	adhesive
Number of positions	9
Number of keys	12 (4 x 3)
Number of socket pins	9
Technology	Conductive silver technology
Embossing	Dome embossing 11 x 11 mm

Dimensions

Dimensions	70 mm x 69 mm
Pitch	2.54 mm
Length	100.5 mm (Membrane cable)

Membrane keypad - KP HCS C-MIN-P K12 C3 P9 - 2203566

Technical data

Ambient conditions

Ambient temperature (storage/transport)	-20 °C ... 70 °C
Ambient temperature (operation)	-40 °C ... 80 °C

Packaging details

Pieces per package	1
Denomination packing units	Pcs.

Classifications

eCl@ss

eCl@ss 10.0.1	27182702
eCl@ss 5.1	27180506
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

Accessories

Additional products

Electronic housing - HCS-C MINI-P 1W C C C 7035 - 2203153



Handheld housing, C-Mini-Plus, light gray, consisting of two half shells with screws, front 1.1 mm recessed, with window and keypad slot

Electronic housing - HCS-C MINI-P 1W C 1 1 7035 - 2203155



Handheld housing, C-Mini-Plus, light gray, consisting of two half shells, two front plates with screws, front 1.1 mm recessed, with window and keypad slot

Membrane keypad - KP HCS C-MIN-P K12 C3 P9 - 2203566

Accessories

Electronic housing - HCS-C MINI-P 1W 2AA C C 7035 - 2203157



Handheld housing, C-Mini-Plus, light gray, consisting of two half shells, screws. Front 1.1 mm recessed, with window and keypad slot, battery compartment cover and battery contacts for 2 AA batteries

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2203566