

Mounting material - PSD-S ME T-M 400 - 2700158

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Tube, 400 mm high, Ø 25 mm

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 491495
GTIN	4046356491495

Technical data

Dimensions

Diameter	25 mm
Height	400 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 60 °C
---------------------------------	------------------

General

Material	Anodized aluminum
Color	silver
Weight	120 g
Mounting position	any
Mounting type	Tube mounting
	Base mounting


Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Mounting material - PSD-S ME T-M 400 - 2700158

Dimensional drawing



Classifications

eCl@ss

eCl@ss 10.0.1	27371236
eCl@ss 4.0	27143200
eCl@ss 4.1	27143200
eCl@ss 5.0	27371200
eCl@ss 5.1	27371200
eCl@ss 6.0	27371200
eCl@ss 7.0	27371236
eCl@ss 8.0	27371236
eCl@ss 9.0	27371236

ETIM

ETIM 3.0	EC001155
ETIM 4.0	EC001155
ETIM 5.0	EC001155
ETIM 6.0	EC001155
ETIM 7.0	EC001155

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	39121311
UNSPSC 13.2	39121311
UNSPSC 18.0	46171604
UNSPSC 19.0	46171604
UNSPSC 20.0	46171604
UNSPSC 21.0	46171604

Mounting material - PSD-S ME T-M 400 - 2700158

Approvals

Approvals

Approvals

EAC / EAC

Ex Approvals

Approval details

EAC		EAC-Zulassung
-----	---	---------------

EAC		RU *- DE.A*30.B.00237
-----	--	--------------------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2700158](#)