

T distributor - PLD E 608-CO-MS/FS/FR - 2702310

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



T-distributor with 2 sockets and one connector for series connection, black, 3-pos.

RoHS

Key Commercial Data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 055626 113364
GTIN	4055626113364

Technical data

General

Type	T-distributor
Color	black
Number of positions	3
Note number of positions	2+PE

Ambient conditions

Degree of protection	IP20
	IP40 (plugged in)
Ambient temperature (operation)	70 °C
Ambient temperature (storage/transport)	-30 °C ... 70 °C

Electrical characteristics

Rated current	16 A (according to EN 61984 at 70 °C)
Rated voltage (I/2)	250 V
Rated surge voltage (I/2)	2.5 kV

Mechanical characteristics

QUICKON connectability	5 (according to EN 61984)
------------------------	---------------------------

T distributor - PLD E 608-CO-MS/FS/FR - 2702310

Technical data

Mechanical characteristics

Insertion/withdrawal cycles	10 (according to EN 61984)
-----------------------------	----------------------------

Material data

Contact material	Brass
Contact surface material	surface-protected
Flammability rating according to UL 94	V2
Degree of pollution	2

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27119290
eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440102
eCl@ss 8.0	27119220
eCl@ss 9.0	27119290

ETIM

ETIM 5.0	EC002557
ETIM 6.0	EC002061

UNSPSC

UNSPSC 13.2	39121413
UNSPSC 18.0	39111541
UNSPSC 19.0	39111541
UNSPSC 20.0	39111541
UNSPSC 21.0	39111541

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2702310](#)