

Disconnect strip - CT 10-TL - 2765356

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



LSA-PLUS disconnect strip to hold the CTM and CT 10 protection modules. Version: 10 double conductors, dimension A: 124 mm.

Your advantages

- ✓ LSA-PLUS disconnect strip
- ✓ For accommodating CT and CTM protective plugs

RoHS

Key Commercial Data

Packing unit	5 pc
GTIN	 4 017918 066253
GTIN	4017918066253

Technical data

Dimensions

Height	22 mm
Width	124 mm
Depth	53 mm

General

Flammability rating according to UL 94	V0
Color	gray
Mounting type	auf LSA-PLUS-Montagebügel
Type	LSA-PLUS module

Protective circuit

Surge protection fault message	none
--------------------------------	------

Connection data

Connection method	Insulation displacement connection
Connection method IN	IDC terminal block

Disconnect strip - CT 10-TL - 2765356

Technical data

Connection data


Connection method OUT	IDC terminal block
-----------------------	--------------------

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing



Classifications

eCl@ss

eCl@ss 4.0	27130800
------------	----------

Disconnect strip - CT 10-TL - 2765356

Classifications

eCl@ss

eCl@ss 4.1	27130800
eCl@ss 5.0	27130800
eCl@ss 5.1	27130800
eCl@ss 6.0	27130800
eCl@ss 7.0	27130807
eCl@ss 8.0	27139202
eCl@ss 9.0	27139202

ETIM

ETIM 2.0	EC000943
ETIM 3.0	EC000943
ETIM 4.0	EC000943
ETIM 5.0	EC002497
ETIM 6.0	EC000943
ETIM 7.0	EC000943

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620
UNSPSC 18.0	39121620
UNSPSC 19.0	39121620
UNSPSC 20.0	39121620
UNSPSC 21.0	39121620

Approvals

Approvals

Approvals

EAC / EAC

Ex Approvals

Approval details

Disconnect strip - CT 10-TL - 2765356

Approvals

EAC		EAC-Zulassung
-----	---	---------------

EAC		RU C- DE.*09.B.00169
-----	---	-------------------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2765356