

## Cover profile - CD-HF COVER 25 - 3240369

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cover for cable duct, light gray, halogen-free, width: 25 mm, length: 2000 mm

RoHS

### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 14 pc                                                                                                   |
| GTIN         | <br>4 046356 508544 |
| GTIN         | 4046356508544                                                                                           |

### Technical data

#### Dimensions

|            |         |
|------------|---------|
| Length (b) | 2000 mm |
| Width (a)  | 25 mm   |
| Height (c) | 14.4 mm |

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 90 °C |
|---------------------------------|------------------|

#### General

|                                        |              |
|----------------------------------------|--------------|
| Color                                  | light gray   |
| Components                             | halogen-free |
| Flammability rating according to UL 94 | V0           |
| Material                               | PC/ABS       |
| Result                                 | Test passed  |
| R22                                    | HL 1 - HL 3  |
| R23                                    | HL 1 - HL 3  |
| R24                                    | HL 1 - HL 3  |

#### Standards and Regulations

|                                        |    |
|----------------------------------------|----|
| Flammability rating according to UL 94 | V0 |
|----------------------------------------|----|

## Cover profile - CD-HF COVER 25 - 3240369

### Technical data

#### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27400776 |
| eCl@ss 4.0    | 27140600 |
| eCl@ss 4.1    | 27140600 |
| eCl@ss 5.0    | 27140600 |
| eCl@ss 5.1    | 27140600 |
| eCl@ss 6.0    | 27400700 |
| eCl@ss 7.0    | 27400776 |
| eCl@ss 8.0    | 27400776 |
| eCl@ss 9.0    | 27400776 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000012 |
| ETIM 3.0 | EC000012 |
| ETIM 4.0 | EC000727 |
| ETIM 5.0 | EC000727 |
| ETIM 6.0 | EC000727 |
| ETIM 7.0 | EC000727 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30101815 |
| UNSPSC 7.0901 | 30101815 |
| UNSPSC 11     | 30101815 |
| UNSPSC 12.01  | 30101815 |
| UNSPSC 13.2   | 39131712 |
| UNSPSC 18.0   | 39131712 |
| UNSPSC 19.0   | 39131712 |
| UNSPSC 20.0   | 39131712 |
| UNSPSC 21.0   | 39131712 |

### Approvals

#### Approvals

#### Approvals

VDE Zeichengenehmigung

## Cover profile - CD-HF COVER 25 - 3240369

### Approvals

---

Ex Approvals

---

### Approval details

VDE Zeichengenehmigung



[http://www2.vde.com/de/Institut/Online-Service/  
VDE-gepruefteProdukte/Seiten/Online-Suche.aspx](http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx)

40028972

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3240369](#)