

Screw connection - WP-G BRASS IP40 PG11 - 3241039

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland made from brass with Pg thread, IP40 protection

RoHS

Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 711753
GTIN	4046356711753

Technical data

Dimensions

Length (b)	30 mm
Width (a)	27 mm
Height (c)	30 mm
Wrench size	23 mm
Inner diameter (f)	11.5 mm
Outside diameter	17 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
Degree of protection	IP40

General

Color	brass
Type	Straight
	Outer thread
Components	halogen-free
Material	Brass

Screw connection - WP-G BRASS IP40 PG11 - 3241039

Technical data

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Classifications

eCl@ss

eCl@ss 10.0.1	27430310
eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	21132000
eCl@ss 5.1	21132000
eCl@ss 6.0	21132000
eCl@ss 7.0	27439203
eCl@ss 8.0	27439203
eCl@ss 9.0	27430310

ETIM

ETIM 3.0	EC000519
ETIM 4.0	EC000519
ETIM 5.0	EC001180
ETIM 6.0	EC001180
ETIM 7.0	EC001180

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	40141734
UNSPSC 18.0	40141734
UNSPSC 19.0	40141734
UNSPSC 20.0	40141734
UNSPSC 21.0	40141734

Approvals

Approvals

Approvals

VDE Zeichengenehmigung

Screw connection - WP-G BRASS IP40 PG11 - 3241039

Approvals

Ex Approvals

Approval details

VDE Zeichengenehmigung



<http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx>

Accessories

Accessories

Corrugated pipe

Protective hose - WP-STEEL ZC 17 - 3240698



Protective hose in galvanized steel

Protective hose - WP-STEEL S 17 - 3240863



Protective hose in stainless steel

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3241039](#)