

Thermal transfer printer - THERMOMARK ROLL X1 - 5146723

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Thermal transfer printer for material off the roll up to a diameter of 200 mm

Your advantages

- ✓ Maintenance-free operation with proven thermal transfer printing technology
- ✓ Easy to control with the PROJECT COMPLETE software
- ✓ For all labels and shrink sleeves
- ✓ Easy operating concept based on user-friendly touch screen entry
- ✓ High-quality, fast labeling
- ✓ The THERMOMARK ROLL can print markers supplied in roll format for terminal, conductor, cable, and device marking applications
- ✓ USB and Ethernet connections

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 714617
GTIN	4046356714617

Technical data

General

Interface	10/100 Mbps Ethernet
	USB 2.0
Weight	5 kg

Dimensions

Length	412 mm
Height	245 mm
Width	380 mm

Connection data

Minimum voltage	100 V AC
-----------------	----------

Thermal transfer printer - THERMOMARK ROLL X1 - 5146723

Technical data

Connection data

Max. voltage	240 V AC
Additional text	50 Hz ... 60 Hz

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27060700
eCl@ss 4.1	27060700
eCl@ss 5.0	27400200
eCl@ss 5.1	27400200
eCl@ss 6.0	19140100
eCl@ss 7.0	19140104
eCl@ss 8.0	19140104
eCl@ss 9.0	19140104

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC001672
ETIM 5.0	EC001672
ETIM 6.0	EC001672
ETIM 7.0	EC001672

UNSPSC

UNSPSC 6.01	27121706
UNSPSC 7.0901	27121706
UNSPSC 11	27121706
UNSPSC 12.01	27121706
UNSPSC 13.2	43212108
UNSPSC 19.0	43212108

Accessories

Accessories

Ink ribbon

Thermal transfer printer - THERMOMARK ROLL X1 - 5146723

Accessories

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., width: 110 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 110 BU - 0829544



Ink ribbon, width: 110 mm, color: blue

Ink ribbon - THERMOMARK-RIBBON 110 GN - 0829542



Ink ribbon, width: 110 mm, color: green

Ink ribbon - THERMOMARK-RIBBON 110 RD - 0829543



Ink ribbon, width: 110 mm, color: red

Ink ribbon - THERMOMARK-RIBBON 110-EML-HT - 0800342



Ink ribbon, for roll printer for printing product group EML-HT..., width: 110 mm, color: black

Thermal transfer printer - THERMOMARK ROLL X1 - 5146723

Accessories

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 110 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 110-WMSU WH - 0801359



Ink ribbon, for roll printer for printing product group WMS... (black), width: 110 mm, color: white

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 64 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 64-WMSU WH - 0801361



Ink ribbon, for roll printer for printing product group WMS... (black), width: 64 mm, color: white

Ink ribbon - THERMOMARK-RIBBON 110-WMTB HF - 5148007



Ink ribbon, for roll printer for printing product groups WMTB HF..., WMS-2 HF..., TMT..., and EMT..., width: 110 mm, color: black

Mounting material

Thermal transfer printer - THERMOMARK ROLL X1 - 5146723

Accessories

Pressure roller - TR-PRESSURE ROLLER DR4-50 - 0801800

Pressure roller



Pressure roller - TR-PRESSURE ROLLER STANDARD - 0801802

Pressure roller



Planning and marking software

Software - CLIP-PROJECT ADVANCED - 5146040



Multilingual software for convenient configuration of Phoenix Contact products on standard DIN rails.

Software - CLIP-PROJECT PROFESSIONAL - 5146053



Multilingual software for terminal strip configuration. A marking module enables the professional marking of markers and labels for identifying terminal blocks, conductors and cables, and devices.

Printing system accessories

Cutter - THERMOMARK ROLL X1 CUTTER - 5146765



Cutter, for the THERMOMARK ROLL X1

Thermal transfer printer - THERMOMARK ROLL X1 - 5146723

Accessories

Cutter - THERMOMARK ROLL X1 CUTTER/P - 5146766



Perforation cutter, for the THERMOMARK ROLL X1, cutter width: 60 mm, suitable for: WMS continuous media, TMT (EX9,5)R, TMT2 (EX11)R, and EMT (EX15)R

Transport case - THERMOMARK ROLL X1-CASE - 5146724



Transport case for THERMOMARK ROLL X1 thermal transfer printer, rounded profile case with aluminum frame

Cart for printer - TL CASE TROLLY - 0803337



Trolley for the transport cases for THERMOMARK LINE and THERMOMARK ROLL X1

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

Media hub - THERMOMARK-ERH 500 - 5146309



External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm

Thermal transfer printer - THERMOMARK ROLL X1 - 5146723

Accessories

Label dispenser - THERMOMARK ROLL X1 -DISPENSER - 1014401



Dispensing device for labels with a height of 10 - 200* mm (*depending on material), for the THERMOMARK ROLL X1

Spare locator - TR X1-MARGIN STOP - 1014407



Spare locator

Replacement part - TR X1-TEAR-OFF PLATE - 1014408



Replacement part

Packaging - TR X1-PACKAGE - 1014409

Packaging

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

5146723