

## Screw - FTP SCREW M3X4,5 - 3069467

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Screw, for attaching cable lugs to FAME test plugs, with cover, without test point, length: 4.5 mm, color: silver/black

The figure shows a similar screw with nut

RoHS

### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 30 pc                                                                                                   |
| Minimum order quantity | 30 pc                                                                                                   |
| GTIN                   | <br>4 055626 166865 |
| GTIN                   | 4055626166865                                                                                           |

### Technical data

#### General

|                     |              |
|---------------------|--------------|
| Color               | silver/black |
| Insulating material | PA           |
| Material            | Brass        |

#### Dimensions

|        |        |
|--------|--------|
| Length | 4.5 mm |
|--------|--------|

#### General

|                                          |                                                                        |
|------------------------------------------|------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 85 °C                                                       |
| Ambient temperature (storage/transport)  | -25 °C ... 55 °C (For a short time, not exceeding 24 h, -60 to +70 °C) |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                          |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                        |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                        |

#### Connection data

|                       |        |
|-----------------------|--------|
| Screw thread          | M3     |
| Tightening torque max | 0.6 Nm |

# Screw - FTP SCREW M3X4,5 - 3069467

## Technical data

### Environmental Product Compliance

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27141190 |
| eCl@ss 4.0    | 27141100 |
| eCl@ss 4.1    | 27141100 |
| eCl@ss 5.0    | 27141100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27149200 |
| eCl@ss 7.0    | 27149214 |
| eCl@ss 8.0    | 27149214 |
| eCl@ss 9.0    | 27141190 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000897 |
| ETIM 3.0 | EC000897 |
| ETIM 4.0 | EC002255 |
| ETIM 5.0 | EC002848 |
| ETIM 6.0 | EC002848 |
| ETIM 7.0 | EC002848 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211812 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121411 |
| UNSPSC 12.01  | 39121411 |
| UNSPSC 13.2   | 39121410 |
| UNSPSC 18.0   | 39121410 |
| UNSPSC 19.0   | 39121410 |
| UNSPSC 20.0   | 39121410 |
| UNSPSC 21.0   | 39121410 |

## Approvals

### Approvals

Approvals

EAC

## Screw - FTP SCREW M3X4,5 - 3069467

### Approvals

Ex Approvals

---

#### Approval details

EAC



RU C-  
DE.A\*30.B.01742

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

3069467