

Cable tie - WT-STEEL SH 7,9X838 - 3240766

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable binders, made from rust-free stainless steel (AISI 316), suitable for the harshest of ambient conditions (for example, salt water), with ball lock, for quick and secure bundling and fastening

RoHS

Key Commercial Data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 046356 704847
GTIN	4046356704847

Technical data

Dimensions

Length (b)	360 mm
Width (a)	4.8 mm
Max. material thickness	0.25 mm

Ambient conditions

Ambient temperature (operation)	-80 °C ... 538 °C
Ambient temperature (assembly)	-80 °C ... 538 °C

General

Color	silver
Type	Steel strip
Components	free from silicone and halogen
Material	Stainless steel 1.4401/AISI 316
Tensile strength	1335 N

Standards and Regulations

Resistance to UV radiation	yes
----------------------------	-----

Environmental Product Compliance

Cable tie - WT-STEEL SH 7,9X838 - 3240766

Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27140702
eCl@ss 4.0	27140700
eCl@ss 4.1	27140700
eCl@ss 5.0	27140700
eCl@ss 5.1	27140700
eCl@ss 6.0	27140700
eCl@ss 7.0	27140702
eCl@ss 8.0	27140702
eCl@ss 9.0	27140702

ETIM

ETIM 3.0	EC000046
ETIM 4.0	EC000046
ETIM 5.0	EC000046
ETIM 6.0	EC000046
ETIM 7.0	EC000046

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703
UNSPSC 18.0	39121731
UNSPSC 19.0	39121731
UNSPSC 20.0	39121731
UNSPSC 21.0	39121731

Approvals

Approvals

Approvals

LR

Cable tie - WT-STEEL SH 7,9X838 - 3240766

Approvals

Ex Approvals

Approval details

LR		http://www.lr.org/en
----	---	---

Accessories

Accessories

Universal tools

Cable tie tool - UNIFOX-CT M 7,9 - 1212610



Cable binder pliers, for steel cable binders with a width of up to 7.9 mm, for a material thickness of up to 0.3 mm

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3240766](#)