

Insert label - EMT (62X10)R YE CUS - 0830252

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Snap-in marker, for marking Inline modules, labeled according to customer requirements

The figure shows the EMT
(50/28x13)R version

Product Features

- ✓ Insertable conductor marking for marking collars
- ✓ Thanks to their special shape, insert labels remain securely inside the collar once inserted
- ✓ Insert labels for marking various marking collars



Key commercial data

Packing unit	1
GTIN	 4 046356 633086
Custom tariff number	39191080

Technical data

Dimensions

Length (b)	62 mm
Width (a)	10 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C / 50 % relative humidity

General

Color	yellow
Components	free from silicone and halogen
Material	Polyester

Insert label - EMT (62X10)R YE CUS - 0830252

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	500
Number of individual labels per row	1
RoHS compliant	Yes
Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
	5145274 THERMOMARK X1.1
	5146231 THERMOMARK X1.2
	5145313 THERMOMARK S1
	5146257 THERMOMARK S1.1
Ink ribbon	5145384 THERMOMARK-RIBBON 110
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Foil strength	175 µm
Marking mounting type	snapped into marker carrier

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

Insert label - EMT (62X10)R YE CUS - 0830252

Classifications

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0830252](#)