

Conductor marking collar - SD-WMS 3 (CH)R YE:S - 0825667:S

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marking collar, labeled with the capital letter: Letters, yellow, width: 3.2 mm, the dimensions of the replacement product differ from the previous product!

RoHS

Key Commercial Data

Packing unit	500 pc
GTIN	 4 046356 419628
GTIN	4046356419628

Technical data

Color	yellow
Flammability rating according to UL 94	V0
Components	Free from silicone and cadmium

Ambient conditions

Temperature range	-30 °C ... 60 °C
-------------------	------------------

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27400400
eCl@ss 6.0	27149100

Conductor marking collar - SD-WMS 3 (CH)R YE:S - 0825667:S

Classifications

eCl@ss

eCl@ss 7.0	27149129
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001530
ETIM 6.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 19.0	39131504

Accessories

Accessories

Assembly tool

Alignment tool for cable markers - SD-WMS 3 TOOL - 0826462



Alignment tool for cable markers, Bare metallic, labeled, mounting type: thread on, cable diameter range: 1.3 ... 3 mm

Mounting material

Magazine box for conductor marking collar - SD-WMS CASE - 0826501



Metal box for storing SD-WMS marking collars in the form of a roll

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0825667:S