

# Data plug - CUC-V14-C1ZNI-S/R4IV8:10 - 1464019

<https://www.phoenixcontact.com/in/products/1464019>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

---



---

## Your advantages

- Push-pull ADVANCE connector
- Locking system to prevent inadvertent removal
- Protected data transmission, thanks to 360° shielding concept
- High resistance to ESD and EMC for reliable transmission

# Data plug - CUC-V14-C1ZNI-S/R4IV8:10 - 1464019



<https://www.phoenixcontact.com/in/products/1464019>

## Commercial Data

Order Key	1464019
Packing unit	10 pc
Minimum order quantity	10 pc
Sales Key	ABN
GTIN	4046356790055
Weight per Piece (including packing)	22.2 GRM
Weight per Piece (excluding packing)	22.2 GRM
Customs tariff number	85366990

# Data plug - CUC-V14-C1ZNI-S/R4IV8:10 - 1464019

<https://www.phoenixcontact.com/in/products/1464019>

## Technical Data

### Cable / line

#### Cable structure

Cable diameter	5.5 mm ... 10 mm
----------------	------------------

### Environmental and real-life conditions

Degree of protection	IP65/IP67
----------------------	-----------

### Notes

#### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

### Electrical properties


Rated voltage (III/3)	72 V (DC)
-----------------------	-----------

### Mechanical properties

#### Interlock

Locking type	Push Pull
--------------	-----------

### Dimensions

Dimensional drawing	
Width	22.4 mm
Height	34 mm
Length	95 mm

### Material specifications

Housing surface material	Nickel-plated
Housing material	Zinc die-cast

### Characteristics

Shielded	no
----------	----

# Data plug - CUC-V14-C1ZNI-S/R4IV8:10 - 1464019



<https://www.phoenixcontact.com/in/products/1464019>

## Standards and regulations

Standards/specifications	IEC PAS 61076-3-117
--------------------------	---------------------

## Product properties


Locking type	Push Pull
--------------	-----------

# Data plug - CUC-V14-C1ZNI-S/R4IV8:10 - 1464019

<https://www.phoenixcontact.com/in/products/1464019>

## Drawings

Dimensional drawing




# Data plug - CUC-V14-C1ZNI-S/R4IV8:10 - 1464019



<https://www.phoenixcontact.com/in/products/1464019>

## Approvals

cULus Recognized 

Nominal voltage $U_N$	56.5 V
Nominal current $I_N$	0.175 A

Phoenix Contact 2020 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.  
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.11.30262800  
[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1464019](#)