


THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

| REVISION |             |      |          |
|----------|-------------|------|----------|
| REV.     | DESCRIPTION | DATE | APPROVED |
|          |             |      |          |
|          |             |      |          |
|          |             |      |          |



#### CONNECTION

CN1 CN2

1 ——— RED ——— 1

2 ——— WHITE ——— 2  
3 ——— GREEN ——— 3

4 ——— BLACK ——— 4

SHELL ——— BRAID&DRAIN ——— SHELL

#### NOTES:

- CABLE: UL2725  
28AWGx1PR+24AWGx2C+ AEB(AL) 65%  
OUTER JACKET: BLACK, OD: 4.5 ± 0.2mm
- CONNECTOR: USB 2.0 A TYPE MALE  
INSULATOR: WHITE PBT  
PIN G/F  
NICKEL PLATED SHELL
- CONNECTOR: USB 2.0 A TYPE MALE  
INSULATOR: WHITE PBT  
PIN G/F  
NICKEL PLATED SHELL
- PVC MOLDED: COLOR 45P BLACK
- ELECTRICAL TEST:  
<1>.100% OPEN SHORT & MISS WIRE TEST  
<2>.INSULATION RESISTANCE: DC300V 10M ohm MIN.  
<3>.CONDUCTOR RESISTANCE: 2 ohm MAX.
- PACKING: 1PC/POLYBAG W/ LABEL

**CONTROLLED**

| Dim range (mm) | Tolerance +/- (mm) | Qualtek Electronics Corp.<br>WCI DIVISION   |                |                 |
|----------------|--------------------|---|----------------|-----------------|
|                |                    | Part Number: 3021059-01M <span style="border: 1px solid green; padding: 2px;">RoHS Compliant</span> |                |                 |
| 0-1            | 0.15               | Description:<br>USB 4P(A)/M - USB 4P(A)/M   |                |                 |
| 1-6            | 0.20               |   |                |                 |
| 6-18           | 0.30               | UNIT: mm  |                |                 |
| 18-50          | 0.50               |   |                |                 |
| 50-120         | 0.70               | Drawn / Date  | Checked / Date | Approved / Date |
| 120-250        | 0.90               | R. Nuti<br>09-25-17   | 09-25-17       | LY / 09-25-17   |
| 250-500        | 1.20               |   |                |                 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Qualtek:

3021059-01M