

Contact insert - HC-B 16-EBUQ-2,5-OLOGO - 1605577

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Female insert, 16-pos., QUICKON connection, marking 1-x


Product Description

Contact insert

With QUICKON connection technology, the wires are connected with just a turn of the screwdriver. The wires do not have to be stripped first. This reduces connection time by at least 60%.

RoHS

Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 940782
GTIN	4017918940782

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

General

Note	For HEAVYCON ADVANCE and HEAVYCON housing of B16 type. Coding using the CP-HC (1686478) coding profile. HC-B6.../ HC-B10... for two coding profiles. HC-B16.../ HC-B24... for 4 coding profiles. Connectors may be operated only when there is no load/voltage.
	Connectors may be operated only when there is no load/voltage.
Size	B16
	B32
Number of positions	16
Flammability rating according to UL 94	V0
Assembly instructions	To ensure correct use, installation in housing with IP54 protection or better is required

Contact insert - HC-B 16-EBUQ-2,5-OLOGO - 1605577

Technical data

General


Connection	For housings of type B16/B32. Connectors may only be actuated when there is no load/voltage.
------------	----------------------------------------------------------------------------------------------

Standards and Regulations


Flammability rating according to UL 94	V0
----------------------------------------	----

Drawings

Schematic diagram




Diagram




The figure shows the derating diagram of various series B contact inserts (B6 to B24), conductor cross section 2.5 mm²

Dimensional drawing



Female insert

Dimensional drawing



Mounting cutout when used without housing

Approvals

Approvals

Approvals


EAC

Ex Approvals

Approval details

Contact insert - HC-B 16-EBUQ-2,5-OLOGO - 1605577

Approvals

EAC		RU C- DE.AI30.B.01102
-----	-----------------------------------------------------------------------------------	--------------------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1605577