



# PSC-61000A-C 6V 1A

Sealed Lead Acid Battery Charger  
A-C Battery Charger Series


## FEATURES

- Universal input voltage range 10VAC - 240VAC
- Automatic, current sensing dual-rate charging for efficient, care-free and safe operation
- LED indicators
- Alligator clip connectors with insulated sleeves

## APPROVALS

- Approved for transport by air. D.O.T., I.A.T.A., F.A.A. and C.A.B. certified
- ISO9001:2015 – Quality management systems
- ETL
- DOE
- FCC
- CE

## CHARGER CHARACTERISTICS



## GLOBAL HEADQUARTERS (USA AND INTERNATIONAL EXCLUDING EMEA)

**Power-Sonic Corporation**  
365 Cabela Dr Suite 300,  
Reno, Nevada 89523  
USA  
T: +1 619 661 2020  
E: customer-service@power-sonic.com

## POWER-SONIC EMEA (EMEA – EUROPE, MIDDLE EAST AND AFRICA)

Smitspol 4, 3861 RS Nijkerk,  
The Netherlands  
T NL: + 31 33 7410 700  
T UK: + 44 1268 560 686  
T FR: + 33 344 32 18 17  
E: salesEMEA@power-sonic.com

## PERFORMANCE SPECIFICATIONS

### Input Specs

AC input voltage rating	100Vac-240Vac
AC input frequency	47Hz-63Hz
AC input current	0.16A@115Vac/0.11A@230Vac
AC input power	13.5W
AC static state current	30mA

### Output Specs

Output voltage range	5-7.5Vdc
Output current	1A-6Vdc
Output power	7.8W
Bulk charge current rating	1A
Bulk charge voltage rating	7.35Vdc
Float charge voltage rating	6.7Vdc
Light switching current	250mA
Charging capacity range	5Ah to 12Ah

### General Specs

Efficiency	0.58
Over load protection	<1.5A
Short circuit protection	Yes
Reversed polarity connectors protection	Yes
Operating temperature	0°C-40°C
Storage temperature	-30°C-85°C
Net weight	90g
Dimensions	80*50*57mm
Enclosure	Plastic Case
Application	Indoor
Charger type	Wall mounting
Plug type	Type A (NEMA 1 - 15)

### Safety Specs

Withstand voltage (Hi-Pot)	3000Vac ≤ 10mA (60s)
Insulation resistance	>100MΩ @500Vdc
Safety standard	ETL
Compliance	FCC

### LED Indicator Status

Green LED on	No load or float charge
Red LED on	Fast charge

## FURTHER INFORMATION

Please refer to our website [www.power-sonic.com](http://www.power-sonic.com) for a complete range of useful downloads, such as product catalogs, material safety data sheets (MSDS), ISO certification, etc.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Power-Sonic:

PSC-61000ACX