





| SPECIFICATIONS               |              |       |
|------------------------------|--------------|-------|
| PARAMETERS                   | VALUES       | UNIT  |
| RATED VOLTAGE                | 12           | Vp-p  |
| OPERATING VOLTAGE RANGE      | 1 ~ 60       | Vp-p  |
| RATED CURRENT (MAX @ 25Vp-p) | 40           | mA    |
| CAPACITANCE                  | 30,000 ± 30% | pF    |
| MINIMUM SPL @ 10 CM          | 100          | dBA   |
| RESONANT FREQUENCY           | 3,250 ± 500  | Hz    |
| OPERATING TEMPERATURE        | -30 ~ +80    | °C    |
| STORAGE TEMPERATURE          | -40 ~ +85    | °C    |
| HOUSING MATERIAL             | PBT (BLACK)  | -     |
| TERMINAL MATERIAL            | Au plated Cu | -     |
| WEIGHT                       | 11           | grams |

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.  
©2003, Projects Unlimited Inc.

| REVISION HISTORY |                               |            |          |
|------------------|-------------------------------|------------|----------|
| LTR              | DESCRIPTION                   | DATE       | APPROVED |
| -                | RELEASED FROM ENGINEERING     | 11/11/2014 |          |
| A                | REVISED CPACITANCE UNIT TO pF | 4/16/2020  | M.L.     |



SOUND EMISSION  
HOLE Ø9.8


NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
3. THIS PART IS RoHS 2011/65/EU COMPLIANT.

UNLESS OTHERWISE SPECIFIED:  
ALL PURCHASES ARE SUBJECT TO AND INCORPORATE THE PUI AUDIO TERMS AND CONDITIONS SALE FOUND AT [http://www.puiaudio.com/pdf/terms\\_conditions.pdf](http://www.puiaudio.com/pdf/terms_conditions.pdf) (paper copy available upon request).  
DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.

AT-4032-TT-R.idw

SIZE  
**A3**

|   |           |            |                     |             |            |                                |
|---|-----------|------------|---------------------|-------------|------------|--------------------------------|
| Designed by   | Date      | Checked by | Date                | Approved by | Date       | Drawn Date                     |
| T.E.S.  | 11/3/2014 | M.L.       | 11/11/2014          | B.R         | 11/11/2014 | 11/3/2014                      |
|  |           |            | <b>AT-4032-TT-R</b> |             |            |                                |
|   |           |            | Transducer (Piezo)  |             |            | Edition<br>-<br>Sheet<br>1 / 1 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AT-4032-TT-R](#)