


## CAPTIVE PANEL SCREW — STYLE 2

See page 11 for ordering code  
See page 9 for finish codes  
For non-standard parts  
contact Sales Office



Available with thread  
locking products, see  
page vii

| PART NO. | THD.  | H.D.<br>+.015<br>-.000 | H.L.<br>±.010 | L.<br>±.015 | T.L.<br>+.000<br>-.015 | S.D.<br>±.005 | S.L.<br>±.010 | P.D.<br>+.000<br>-.010 | P.L.<br>±.015 | W.<br>+.005<br>-.000 | D.<br>+.010<br>-.000 | KNURL<br>TPI |
|----------|-------|------------------------|---------------|-------------|------------------------|---------------|---------------|------------------------|---------------|----------------------|----------------------|--------------|
| 0401     | 6-32  | 5/16                   | 5/16          | 1-3/16      | 7/32                   | .095          | 7/8           | .095                   | 3/32          | 3/64                 | 5/64                 | 35           |
| 0402     | 6-32  | 5/16                   | 5/16          | 1-1/4       | 7/32                   | .095          | 15/16         | .095                   | 3/32          | 3/64                 | 5/64                 | 35           |
| 0403     | 8-32  | 5/16                   | 5/16          | 7/16        | 7/32                   | .120          | 1/8           | .120                   | 3/32          | 3/64                 | 5/64                 | 35           |
| 0404     | 8-32  | 5/16                   | 5/16          | 1/2         | 7/32                   | .120          | 3/16          | .120                   | 3/32          | 3/64                 | 5/64                 | 35           |
| 0405     | 8-32  | 5/16                   | 5/16          | 9/16        | 7/32                   | .120          | 1/4           | .120                   | 3/32          | 3/64                 | 5/64                 | 35           |
| 0406     | 8-32  | 5/16                   | 5/16          | 5/8         | 7/32                   | .120          | 5/16          | .120                   | 3/32          | 3/64                 | 5/64                 | 35           |
| 0407     | 8-32  | 5/16                   | 5/16          | 11/16       | 7/32                   | .120          | 3/8           | .120                   | 3/32          | 3/64                 | 5/64                 | 35           |
| 0408     | 8-32  | 5/16                   | 5/16          | 3/4         | 7/32                   | .120          | 7/16          | .120                   | 3/32          | 3/64                 | 5/64                 | 35           |
| 0409     | 8-32  | 5/16                   | 5/16          | 13/16       | 7/32                   | .120          | 1/2           | .120                   | 3/32          | 3/64                 | 5/64                 | 35           |
| 0410     | 8-32  | 5/16                   | 5/16          | 7/8         | 7/32                   | .120          | 9/16          | .120                   | 3/32          | 3/64                 | 5/64                 | 35           |
| 0411     | 8-32  | 5/16                   | 5/16          | 15/16       | 7/32                   | .120          | 5/8           | .120                   | 3/32          | 3/64                 | 5/64                 | 35           |
| 0412     | 8-32  | 5/16                   | 5/16          | 1"          | 7/32                   | .120          | 11/16         | .120                   | 3/32          | 3/64                 | 5/64                 | 35           |
| 0413     | 8-32  | 5/16                   | 5/16          | 1-1/16      | 7/32                   | .120          | 3/4           | .120                   | 3/32          | 3/64                 | 5/64                 | 35           |
| 0414     | 8-32  | 5/16                   | 5/16          | 1-1/8       | 7/32                   | .120          | 13/16         | .120                   | 3/32          | 3/64                 | 5/64                 | 35           |
| 0415     | 8-32  | 5/16                   | 5/16          | 1-3/16      | 7/32                   | .120          | 7/8           | .120                   | 3/32          | 3/64                 | 5/64                 | 35           |
| 0416     | 8-32  | 5/16                   | 5/16          | 1-1/4       | 7/32                   | .120          | 15/16         | .120                   | 3/32          | 3/64                 | 5/64                 | 35           |
| 0417     | 10-24 | 3/8                    | 7/16          | 1/2         | 1/4                    | .130          | 3/32          | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0418     | 10-24 | 3/8                    | 7/16          | 9/16        | 1/4                    | .130          | 5/32          | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0419     | 10-24 | 3/8                    | 7/16          | 5/8         | 1/4                    | .130          | 7/32          | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0420     | 10-24 | 3/8                    | 7/16          | 11/16       | 1/4                    | .130          | 9/32          | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0421     | 10-24 | 3/8                    | 7/16          | 3/4         | 1/4                    | .130          | 11/32         | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0422     | 10-24 | 3/8                    | 7/16          | 13/16       | 1/4                    | .130          | 13/32         | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0423     | 10-24 | 3/8                    | 7/16          | 7/8         | 1/4                    | .130          | 15/32         | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0424     | 10-24 | 3/8                    | 7/16          | 15/16       | 1/4                    | .130          | 17/32         | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0425     | 10-24 | 3/8                    | 7/16          | 1"          | 1/4                    | .130          | 19/32         | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0426     | 10-24 | 3/8                    | 7/16          | 1-1/16      | 1/4                    | .130          | 21/32         | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0427     | 10-24 | 3/8                    | 7/16          | 1-1/8       | 1/4                    | .130          | 23/32         | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0428     | 10-24 | 3/8                    | 7/16          | 1-3/16      | 1/4                    | .130          | 25/32         | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0429     | 10-24 | 3/8                    | 7/16          | 1-1/4       | 1/4                    | .130          | 27/32         | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0430     | 10-24 | 3/8                    | 7/16          | 1-5/16      | 1/4                    | .130          | 29/32         | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0431     | 10-24 | 3/8                    | 7/16          | 1-3/8       | 1/4                    | .130          | 31/32         | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0432     | 10-24 | 3/8                    | 7/16          | 1-7/16      | 1/4                    | .130          | 1-1/32        | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0433     | 10-24 | 3/8                    | 7/16          | 1-1/2       | 1/4                    | .130          | 1-3/32        | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0434     | 10-24 | 3/8                    | 7/16          | 1-9/16      | 1/4                    | .130          | 1-5/32        | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0435     | 10-24 | 3/8                    | 7/16          | 1-5/8       | 1/4                    | .130          | 1-7/32        | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0436     | 10-24 | 3/8                    | 7/16          | 1-11/16     | 1/4                    | .130          | 1-9/32        | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0437     | 10-24 | 3/8                    | 7/16          | 1-3/4       | 1/4                    | .130          | 1-11/32       | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0438     | 10-24 | 3/8                    | 7/16          | 1-13/16     | 1/4                    | .130          | 1-13/32       | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0439     | 10-24 | 3/8                    | 7/16          | 1-7/8       | 1/4                    | .130          | 1-15/32       | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0440     | 10-24 | 3/8                    | 7/16          | 1-15/16     | 1/4                    | .130          | 1-17/32       | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |
| 0441     | 10-24 | 3/8                    | 7/16          | 2"          | 1/4                    | .130          | 1-19/32       | .130                   | 5/32          | 1/16                 | 3/32                 | 35           |



RAF ELECTRONIC  
HARDWARE

95 Silvermine Road, Seymour, Ct. 06483 Phone: 203-888-2133 Fax: 203-888-9860  
e-mail : [info@rafhdwe.com](mailto:info@rafhdwe.com) Web: [www.rafhdwe.com](http://www.rafhdwe.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[RAF Electronic Hardware:](#)

[0411-SS-20](#)