



[ABOUT US](#) [WHAT'S NEW](#) [CONTACT US](#) [SERVICES](#) [QUALITY](#) [SITE MAP](#)

[HOME](#)

[PRODUCTS](#)

[ONLINE CATALOG](#)

[REQUEST QUOTE](#)

[ORDER ONLINE](#)

[CHECK STOCK](#)

[REQUEST PRINT CATALOG](#)

[REQUEST SAMPLES](#)

[ENGINEERING DATA](#)

[DISTRIBUTORS](#)

[CAPABILITIES BROCHURE](#)

CALL NOW:
203 888-2133

PART NO. SEARCH - ENTER 3-4 CHARS:

ENTER

Catalogs: [ASE](#) | [Metric](#) | [Handles & Ferrules](#)

1/4 Hex Male-Female Standoffs

[Home](#) [Previous](#) [Next](#)
[Related Metric](#)

Ordering Code			
xxxx	xxx	x	x
Length	Thread	Material	Finish

PART: 4530-440-AL-9

Enter desired quantities:

Qty 1


Qty 2

Qty 3

[Request Quote](#)

[Check Stock](#)

[Download drawing](#)



Select	Part No.	Length
☐	4530A	7/32
☐	4530	1/4
☐	4530T	9/32
☐	4531	5/16
☐	4531T	11/32
☐	4532	3/8
☐	4532T	13/32
☐	4533	7/16
☐	4533T	15/32
☐	4534	1/2
☐	4534T	17/32
☐	4535	9/16
☐	4535T	19/32
☐	4536	5/8
☐	4536T	21/32
☐	4537	11/16
☐	4537T	23/32
☐	4538	3/4
☐	4538T	25/32
☐	4539	13/16
☐	4539T	27/32
☐	4540	7/8
☐	4540T	29/32

Select	Part No.	Length
☐	4541	15/16
☐	4541T	31/32
☐	4542	1"
☐	4543	1-1/16
☐	4544	1-1/8
☐	4545	1-3/16
☐	4546	1-1/4
☐	4547	1-5/16
☐	4548	1-3/8
☐	4549	1-7/16

Select	Part No.	Length
☐	4550	1-1/2
☐	4551	1-9/16
☐	4552	1-5/8
☐	4553	1-11/16
☐	4554	1-3/4
☐	4555	1-13/16
☐	4556	1-7/8
☐	4557	1-15/16
☐	4558	2"
☐	4559	2-1/8
☐	4560	2-1/4
☐	4561	2-3/8
☐	4562	2-1/2
☐	4563	2-5/8
☐	4564	2-3/4
☐	4565	2-7/8
☐	4566	3"
☐	4567	3-1/4
☐	4568	3-1/2
☐	4569	3-3/4
☐	4570	4"

Select	Code	Thread
☐	256	2-56
☐	440	4-40
☐	632	6-32
☐	832	8-32

Thread Length Code		
Thread	A	B
2-56	3/16	5/32
4-40	1/4	3/16
6-32	3/8	1/4
8-32	7/16	3/8

In short lengths, 'A' will be tapped to maximum depth

Select	Code	Material	RoHS
☐	AL	Aluminum	YES
☐	B	Brass	YES
☐	SS	Stainless Steel	YES
☐	S	Steel	YES
☐	N	Nylon	YES

[Material Specifications](#)

SELECT FINISH:

9-Alodine 1200*

* Finishes ending with an asterisk are not RoHS Compliant

[Ordering non-standard items](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

RAF Electronic Hardware:

[4530A-632-N](#) [4530A-632-SS](#) [4530T-632-N](#) [4530T-632-SS](#) [4531T-632-N](#) [4531T-632-SS](#) [4532T-632-N](#) [4532T-632-SS](#) [4533T-632-N](#) [4533T-632-SS](#) [4534T-632-N](#) [4535T-632-SS](#) [4536T-632-SS](#) [4538T-632-SS](#) [4539T-632-SS](#) [4543-632-N](#) [4545-632-SS](#) [4530-632-N](#) [4530-632-SS](#) [4531-632-SS](#) [4532-632-N](#) [4533-632-N](#) [4533-632-SS](#) [4534-632-N](#) [4534-632-SS](#) [4535-632-N](#) [4535-632-SS](#) [4536-632-SS](#) [4537-632-N](#) [4538-632-SS](#) [4542-632-SS](#) [4530-832-AL](#) [4530-832-SS](#) [4531-832-AL](#) [4531-832-SS](#) [4532-832-AL](#) [4532-832-SS](#) [4533-832-AL](#) [4535-832-AL](#) [4535-832-SS](#) [4536-832-AL](#) [4536-832-SS](#) [4537-832-AL](#) [4537-832-SS](#) [4538-832-SS](#) [4539-832-SS](#) [4534-632-AL](#) [4531-632-AL](#) [4533-632-AL](#) [4530-632-AL](#) [4538-632-B](#) [4532-632-S](#) [4533T-632-AL](#) [4530T-632-AL](#) [4530A-632-AL](#) [4554-632-SS](#) [4531-632-B](#) [4532-632-B](#) [4560-632-N](#) [4536-632-b](#) [4542-832-b](#) [4544-832-al](#) [4542-832-n](#) [4558-632-b](#) [4556-632-al](#) [4548-832-ss](#) [4550-632-b](#) [4550-832-b](#) [4550-832-ss](#) [4530-632-b](#) [4539-632-al](#) [4541-632-al](#) [4533-632-b](#) [4534-832-b](#) [4570-832-ss](#)