



### Main

Product Range	Legacy
Product Type	Socket
Product Compatibility	Relay 788XBXR/XCXR
Number of Terminals	11
Switch Function	3PDT
Contact Composition	3 NO + 3 NC

### Complementary

Rated Current	15 A
[Ue] rated operational voltage	300 V
Contact Terminal Arrangement	Mixed
Connections Terminals	Output screw clamp terminalssolid Output screw clamp terminalsstranded
Tightening Torque	Screw < 1 N.m Screw < 0.8 N.m
Fixing Mode	By screw M3.5, M3.5 panel Clip-on 35 mm DIN rail
Shape of Screw Head	Combination roundhead
Product Weight	1.80 oz (51 g)
Width	141.08 ft (43.00 m)
Depth	2.24 in (57 mm)

### Environment

Ambient Air Temperature for Storage	-40...221 °F (-40...105 °C)
Ambient Air Temperature for Operation	-40...131 °F (-40...55 °C)
Flame Retardance	UL94-V0
Product Certifications	UL CSA CE

### Ordering and shipping details

GTIN	3606480277955
Nbr. of units in pkg.	1
Package weight(Lbs)	1.80 oz (51 g)

### Packing Units


Unit Type of Package 1	PCE
Package 1 Height	3.15 in (8 cm)
Package 1 width	1.69 in (4.3 cm)
Package 1 Length	1.02 in (2.6 cm)
Unit Type of Package 2	BB1

Number of Units in Package 2	10
Package 2 Weight	17.99 oz (510 g)
Package 2 Height	2.13 in (5.4 cm)
Package 2 width	3.15 in (8 cm)
Package 2 Length	8.46 in (21.5 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	250
Package 3 Weight	28.11 lb(US) (12.75 kg)
Package 3 Height	8.46 in (21.5 cm)
Package 3 width	11.61 in (29.5 cm)
Package 3 Length	20.28 in (51.5 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Approximate Dimensions



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[70-463-1](#)