

# Product data sheet

## Characteristics

# 70-782E14-1

Socket, SE Relays, 10A, 17 pins, screw connectors, mixed contact, for 782 relays



### Main

Product Range	Harmony Electromechanical Relays
Product Type	Socket
Product Compatibility	Relay 792XDX Relay 782DXH Diode 70-BSMD Signalling device 70-BSMLG Suppressor module 70-BSMM Jumper wire 16-782CBJ-1
Number of Terminals	14
Switch Function	4PDT
Contact Composition	4 C/O

### Complementary

Rated Current	10 A
[Ue] rated operational voltage	300 V
Contact Terminal Arrangement	Separate
Connections Terminals	Lift terminalsflexible Lift terminalssolid
Tightening Torque	0.8 N.m, AWG 16...AWG 14, copper Screw 0.8 N.m
Fixing Mode	By screw, M3 panel Clip-on 35 mm symmetrical DIN rail
Shape of Screw Head	Combination roundhead
Product Weight	1.98 oz (56 g)
Width	1.06 in (26.9 mm)
Depth	3.11 in (79 mm)

### Environment

Ambient Air Temperature for Storage	-40...221 °F (-40...105 °C)
Ambient Air Temperature for Operation	-40...158 °F (-40...70 °C)
IP Degree of Protection	IP20
Flame Retardance	UL94-V0
Product Certifications	UL CSA CE

### Ordering and shipping details

GTIN	3606480278129
Nbr. of units in pkg.	1
Package weight(Lbs)	1.98 oz (56.0 g)

### Packing Units


Unit Type of Package 1	PCE
Package 1 Height	3.11 in (7.9 cm)
Package 1 width	1.06 in (2.69 cm)
Package 1 Length	3.11 in (7.9 cm)
Unit Type of Package 2	BB1

Number of Units in Package 2	10
Package 2 Weight	19.75 oz (560.0 g)
Package 2 Height	2.85 in (7.25 cm)
Package 2 width	3.54 in (9 cm)
Package 2 Length	5.41 in (13.75 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Weight	24.69 lb(US) (11.2 kg)
Package 3 Height	7.09 in (18 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	18.50 in (47 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Dimensions



(1) : Metal hold-down clip

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[70-782E14-1](#)