

9002AW2

Foot Switch, Harmony, industrial, pedal and side shields, 5A resistive at 600 VAC, SPDT contact, NEMA 2, 4, 13 enclosure



Main

Range	9002AW
Product	Foot switch
Contact Operation	1 step
Certifications	UL Listed CSA
Cable Entry	0.75 inch NPT conduit entrance
Contact Arrangement	SPDT
Enclosure Rating	NEMA 2/4/13
Voltage Rating	600 V AC/DC
Protection	Pedal shield Side shield
Operator Action	Spring return
Rated Breaking Capacity	15 A 120 V AC inductive control circuit UL 508 10 A 240 V AC inductive control circuit UL 508 6 A 480 V AC inductive control circuit UL 508 5 A 600 V AC inductive control circuit UL 508 15 A 120 V AC resistive control circuit UL 508 0.5 A 125 V DC resistive control circuit UL 508
Height	4.84 in (123 mm)
Width	5.39 in (137 mm)
Depth	9.02 in (229 mm)

Ordering and shipping details

Category	21441-9002 AW FOOT SWITCHES
Discount Schedule	CS1
GTIN	785901815921
Nbr. of units in pkg.	1
Package weight(Lbs)	4.64 lb(US) (2.105 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.80 in (14.732 cm)
Package 1 width	5.60 in (14.224 cm)
Package 1 Length	12.00 in (30.48 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	72
Package 2 Weight	335.00 lb(US) (151.953 kg)
Package 2 Height	40.00 in (101.6 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9002AW2](#)