


70S2-01-A-03-F

Relay, SE Relays, solid state, SPST, 3A, 3...60 VDC, 3...15 VDC Uc, MOSFET, printed circuit board mount, solder terminal



Main

Range	Legacy
Product Type	Solid state relay
Maximum output current	3 A DC
Mounting Support	Printed circuit boards
Network Number of Phases	1 phase
Output Voltage	3...60 V DC

Complementary

Input Current Limits	5...40 mA at 3...15 V DC typical
Switch Function	SPST
Contacts Type and Composition	NO
Protection Type	Reverse polarity 3 V DC control
Connections Terminals	Solder terminal
Switching Voltage	1 V DC tripping
Switching Device	Mosfet output DC switching
Surge Current	5 A 1 s
Must Release Voltage	1 V
Voltage Drop	<1.2 V on-state DC
Thermal Resistance	25 °C/W
Leakage Current	10 µA at off-state
Response Time	75 µs (turn-on) 500 µs (turn-off)
Dielectric Strength	2500 V between input and output 2500 V between terminals and chassis
Height	0.88 in (22.25 mm)
Width	1.03 in (26.2 mm)
Depth	1.23 in (31.2 mm)
Product Weight	1.23 oz (35 g)

Environment

Product Certifications	CE
Ambient Air Temperature for Operation	-40...185 °F (-40...85 °C)
Ambient Air Temperature for Storage	-40...257 °F (-40...125 °C)





Ordering and shipping details

GTIN	3606480278365
Nbr. of units in pkg.	1
Package weight(Lbs)	1.16 oz (33.0 g)

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.10 in (2.8 cm)
Package 1 width	1.22 in (3.1 cm)
Package 1 Length	1.30 in (3.3 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	100
Package 2 Weight	7.91 lb(US) (3.59 kg)
Package 2 Height	5.71 in (14.5 cm)
Package 2 width	7.99 in (20.3 cm)
Package 2 Length	10.75 in (27.3 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	400
Package 3 Weight	33.42 lb(US) (15.16 kg)
Package 3 Height	12.40 in (31.5 cm)
Package 3 width	11.61 in (29.5 cm)
Package 3 Length	16.93 in (43 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Connections and Wiring Diagrams



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[70S2-01-A-03-F](#)