

Main

Product Range	Legacy
Product Type	Socket
Product Compatibility	Relay 750XCXR Relay 750XCXH
Number of Terminals	11
Switch Function	3PDT
Contact Composition	3 NO + 3 NC

Complementary

Rated Current	5 A 15 A
[Ue] rated operational voltage	300...600 V
Contact Terminal Arrangement	Mixed
Connections Terminals	Output screw clamp terminalssolid Output screw clamp terminalsstranded
Tightening Torque	Screw < 1 N.m Screw < 0.8 N.m
Fixing Mode	By screw M3.5, M3.5 panel Clip-on 35 mm DIN rail
Shape of Screw Head	Combination roundhead
Product Weight	2.01 oz (57 g)
Width	2.32 in (59 mm)
Depth	2.24 in (57 mm)

Environment

Ambient Air Temperature for Storage	-40...221 °F (-40...105 °C)
Ambient Air Temperature for Operation	-40...131 °F (-40...55 °C)
Flame Retardance	UL94-V0
Product Certifications	UL CSA CE

Ordering and shipping details

GTIN	3606480277979
Nbr. of units in pkg.	1
Package weight(Lbs)	2.01 oz (57.0 g)


Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.16 in (5.48 cm)
Package 1 width	2.32 in (5.9 cm)
Package 1 Length	0.97 in (2.46 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	20.11 oz (570.0 g)
Package 2 Height	2.36 in (6 cm)
Package 2 width	4.21 in (10.7 cm)
Package 2 Length	4.92 in (12.5 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	400
Package 3 Weight	50.27 lb(US) (22.8 kg)
Package 3 Height	13.58 in (34.5 cm)
Package 3 width	11.42 in (29 cm)
Package 3 Length	19.69 in (50 cm)


Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Approximate Dimensions



Connections and Wiring Diagrams



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[70-465-1](#)